

## 1 Port Cat5 USB Extender - Up to 330 ft (100 Meters)

StarTech ID: *USB100EXT*



StarTech.com's USBthere offers simple USB extension, allowing you to place a USB device up to 330ft (100m) away from the computer - 20 times longer than normal USB cable length restrictions. The USB extender is comprised of both local and remote units, which can be connected together to extend the USB connection distance over standard Cat5e Ethernet cable.

Delivering cost-effective USB extension, the USBthere USB extender eliminates the expense of additional hubs, repeaters, power adapters or software, making it perfect for a broad range of applications including security and surveillance devices like USB video cameras etc.

The USBthere is designed to provide dependable, long-lasting USB device performance over long distances, and is backed by StarTech.com's 2-year warranty.

**Please note:** This product is not suitable for use with low speed devices like a USB mouse or keyboard. Please see StarTech.com's [USB110EXT](#) or [USB120EXT](#).

### Applications and Solutions

- Ideal for use with remote digital recorders, USB web cameras, printers, scanners and other full-speed USB devices
- Security/Surveillance

## Features

- Extends the range of one USB device up to 330 feet (100 meters) using standard Cat 5e Ethernet cables
- Compliant with USB 1.1 specifications
- Data transfer rates of up to 12 Mbits/sec
- Requires no external power adapter
- Comes complete with a 6 foot USB cable

## Technical Specifications

- Warranty: 2 Years
- Product Height: 1.18 in [30 mm]
- Product Length: 3.94 in [100 mm]
- Maximum Data Transfer Rate: 12000000 Mbits/Sec
- Operating Temperature: 4 to 40
- Carton Quantity: 70
- Industry Standards: USB 1.1
- Shipping (Package) Weight: 0.84 lb [0.38 kg]
- Product Weight: 3.53 oz [100 g]
- Product Width: 2.76 in [70 mm]
- Extension Distance: 330 feet (100 meters)
- Data Transfer Rate: Up to 12 Mbits/sec
- Local Unit Connectors: Upstream: 1 x 4 pin USB (Type B)

Downstream: 1 x RJ-45

- Remote Unit Connectors: Upstream: 1 x RJ-45

Downstream: 1 x 6 pin USB (Type A)

- USB Hub Support: Up to 5 hubs connected to the local unit
- Dimensions: 3.9 x 2.7 x 1.2 Inches (100 x 70 x 30 mm)
- Weight: 0.2 lbs (0.1 kg)
- Maximum power available to USB at the Remote Unit: 300 mA when the Local Unit is supplied with 500 mA

