

1 Port Cat5 USB Extender - Up to 330 ft (100 Meters)

StarTech ID: *USB100EXT*



StarTech.com's USBthere offers simple USB extension, allowing you to place a USB device up to 330ft (100m) away from the computer - 20 times longer than normal USB cable length restrictions. The USB extender is comprised of both local and remote units, which can be connected together to extend the USB connection distance over standard Cat5e Ethernet cable.

Delivering cost-effective USB extension, the USBthere USB extender eliminates the expense of additional hubs, repeaters, power adapters or software, making it perfect for a broad range of applications including security and surveillance devices like USB video cameras etc.

The USBthere is designed to provide dependable, long-lasting USB device performance over long distances, and is backed by StarTech.com's 2-year warranty.

Please note: This product is not suitable for use with low speed devices like a USB mouse or keyboard. Please see StarTech.com's [USB110EXT](#) or [USB120EXT](#).

Applications

- Ideal for use with remote digital recorders, USB web cameras, printers, scanners and other full-speed USB devices
- Security/Surveillance

Features

- Extends the range of one USB device up to 330 feet (100 meters) using standard Cat 5e Ethernet cables
- Compliant with USB 1.1 specifications
- Data transfer rates of up to 12 Mbps/sec
- Comes complete with a 6 foot USB cable
- Requires no external power adapter

Technical Specifications

Warranty	2 Years
Ports	1
Cabling	Cat 5 UTP
Industry Standards	USB 1.1
Maximum Data Transfer Rate	12000000 Mbits/Sec
Max Distance	100 m / 330 ft
General Specifications	0.2 lbs (0.1 kg)
General Specifications	3.9 x 2.7 x 1.2 Inches (100 x 70 x 30 mm)
General Specifications	300 mA when the Local Unit is supplied with 500 mA
General Specifications	330 feet (100 meters)
General Specifications	Up to 12 Mbps/sec
General Specifications	Up to 5 hubs connected to the local unit
General Specifications	Upstream: 1 x RJ-45 Downstream: 1 x 6 pin USB (Type A)
General Specifications	Upstream: 1 x 4 pin USB (Type B) Downstream: 1 x RJ-45
Color	Black
Enclosure Type	Plastic
Product Length	3.9 in [100 mm]
Product Width	2.8 in [70 mm]
Product Height	1.2 in [30 mm]
Product Weight	3.5 oz [100 g]
Operating Temperature	4 to 40
Shipping (Package) Weight	0.8 lb [0.4 kg]
Included in Package	1 - Local Extender unit
Included in Package	1 - Remote Extender unit
Included in Package	1 - 6 Foot USB Cable
Included in Package	1 - User's Guide

Certifications, Reports and Compatibility

