

USB to 10/100 Mbits/sec. Mini Ethernet Adapter

StarTech ID: USB1100S



When you need a reliable, cost-effective mobile network connection, choose the USB1100S. With full duplex support for data transfer rates up to 200 Mbits/sec., this USB network adapter provides a quick and easy way to add network connectivity to any desktop or notebook computer.

- No need to open up case or have an open CardBus slot: works in any USB 1.1 or 2.0 port
- Full and half duplex support, plus auto-negotiation of 10 and 100 Mbits/sec. connections provides easy connectivity in any Ethernet environment
- Easy Plug and Play setup in Windows

This product is backed by StarTech.com's Lifetime warranty.

Applications

- Connects notebook PC to a network
- Connects PC with no available expansion slots to a network
- Can be a valuable tool when sharing network resources

Features

- Automatically detects 10 or 100 Mbps network speed
- Easily connects your Notebook or PC to an Ethernet network without inserting additional cards
- Built-in LED indicators shows connection speed, link, and activity for easy network diagnostics
- Supports Full-Duplex Ethernet connections
- Easily swap your network connection from one computer to another without any interruptions
- Allows high speed network access and up to 12 Mb/s data transfer

Technical Specifications

Warranty	Lifetime
Connector Type(s)	1 - RJ-45 Female
Connector Type(s)	1 - USB B (4 pin) Female
Maximum Data Transfer Rate	12000000 Kbits/Sec
General Specifications	0 ~ 70 degrees Celsius
General Specifications	1x RJ45 Female & 1x USB type A Male
General Specifications	2.79 x 1.41 x 0.68
General Specifications	3 Indicators (10 Mbps, 100Mbps & Full-Duplex)
General Specifications	3.3V
General Specifications	30 grams
General Specifications	Compatible with current Windows and Linux versions with USB Device Support and Drivers
General Specifications	FCC class - A & CE
General Specifications	IEEE 802.3 & 802.3u
General Specifications	RealTek RTL8150
General Specifications	Up to 12 Mbps
General Specifications	USB Specification 1.0 & 1.1
Color	Beige
Product Length	2.8 in [70.9 mm]
Product Width	1.4 in [35.8 mm]
Product Height	0.7 in [17.3 mm]
LED Indicators	1 - 10 Mbps
LED Indicators	1 - 100 Mbps
LED Indicators	1 - Full Duplex
Operating Temperature	0 ~ 70
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - USB to 10/100 Mini Ethernet Adapter