

USBthere - 4 Port 1640 Foot (500 Meter) Powered USB Extender

StarTech ID: USB204EXTFIB



Boost the distance of your USB connection with the USBthere, a four-port USB extender from StarTech.com. You'll be able to place your USB devices up to 1,650 feet (500m) away from your computer, an incredible 100 times greater than normal USB length restrictions. The Local and Remote units connect using Multimode Fiber Optic Cable and there's no need to buy additional hubs, repeaters or software, you just plug in and go.

Perfect for security and surveillance devices like USB video cameras, digital recorders and other monitoring equipment, the USBthere maintains the USB 1.1 standard with data transfer rates of up to 12 Mbits/sec. With the USBthere, extending the range of your USB devices has never been easier.

Applications

- Ideal for use with remote digital recorders, security/surveillance/monitoring equipment, POS devices, printers, scanners and most other USB devices
- Allows users to extend the distance of existing USB devices up to 500 meters by using Multimode Fiber Optic cables

Features

- Extends the range of USB devices up to 500 meters using fiber optic cables
- Compliant with USB 1.1 specifications
- Data transfer rates of up to 12 Mbits/sec
- Allows you to connect multiple USB devices by cascading up to 4 USB hubs
- Uses standard multimode fiber optic cables with MT-RJ connectors

Technical Specifications

Warranty	2 Years
Ports	4
Cabling	Cat 5 UTP
Industry Standards	USB 1.1
Local Unit Connectors	1 - Fiber Optic MT-RJ Female
Local Unit Connectors	1 - USB B (4 pin) Female
Remote Unit Connectors	1 - Fiber Optic MT-RJ Female
Remote Unit Connectors	4 - USB A (4 pin) Female
Maximum Data Transfer Rate	12 Mbps
Maximum Cable Length	1640 ft [500 m]
Max Distance	500 m / 1650 ft
General Specifications	
General Specifications	1 x 6 ft USB Cable
General Specifications	1 x Local Extender unit
General Specifications	1 x Remote Extender unit
General Specifications	1 x User's Guide
General Specifications	1,650 ft (500 m)
General Specifications	2 x 15V DC (1A) Power Adapter
General Specifications	98SE/2000/ME & XP
General Specifications	Up to 12 Mbits/sec
General Specifications	up to 4 hubs
Color	Black
Enclosure Type	Steel
Product Length	4.2 in [106 mm]
Product Width	4.5 in [114 mm]
Product Height	1.5 in [38 mm]
Product Weight	10.6 oz [300 g]
Output Voltage	15 DC
Output Current	1A
Shipping (Package) Weight	3.1 lb [1.4 kg]
Included in Package	1 - Local Extender unit
Included in Package	1 - Remote Extender unit
Included in Package	1 - 6 ft USB Cable
Included in Package	1 - 15V DC (1A) Power Adapt

Included in Package 1 - User's Guide

Certifications, Reports and Compatibility

