

USB DVI External Dual or Multi Monitor Video Adapter

StarTech ID: *USB2DVIE2*



The USB2DVIE2 USB DVI Multi Monitor External Video Adapter turns an available USB 2.0 port into an external video card DVI port - providing high quality dual-display or multi-monitor capability that can be used in a variety of laptop or desktop applications to increase your productivity.

The device also offers the option of running up to five additional displays simultaneously (using five USB2DVIE2 Multi Monitor External Video Cards). Each connected adapter can be used to further extend the desktop or mirror the image shown on the existing display - all without having to open the computer case to install an additional video card.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications and Solutions

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card

- Add multiple (up to five) monitors / projectors to your computer setup using one USB2DVIE2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Includes easy to use software that allows for screen rotation, multi-display management and EDID monitor detection for increased compatibility with displays
- No power adapter required, easy installation
- Optimal performance at 1440x900 (higher resolutions supported) and ideal for use with 17" to 19" monitors or smaller
- Works with desktop and laptop computers
- Supports the use of DVI to VGA or DVI to HDMI adapters

Technical Specifications

- Warranty: 2 Years
- Product Height: 0.71 in [18 mm]
- Product Length: 3.56 in [90.5 mm]
- Memory: 16MB SDRAM
- OS Compatibility: Window 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2
- Carton Quantity: 40
- Supported Resolutions: Widescreen(16/32 bit):

1680x1050

1440x900

1280x800

1280x768

Standard(16/32 bit):

1600x1200

1400x1050

1280x1024

1280x960

1152x864

1024x768

800x600

- Shipping (Package) Weight: 0.66 lb [0.3 kg]
- Product Weight: 3.25 oz [92 g]
- Product Width: 2.07 in [52.5 mm]
- System and Cable Requirements: One available USB 2.0 port

