

USB to DVI External Dual or Multi Monitor Video Adapter

StarTech ID: USB2DVIE2



The USB2DVIE2 USB DVI Multi Monitor External Video Adapter turns an available USB 2.0 port into an external video card DVI port - providing high quality dual-display or multi-monitor capability that can be used in a variety of laptop or desktop applications to increase your productivity.

The device also offers the option of running up to five additional displays simultaneously (using five USB2DVIE2 Multi Monitor External Video Cards). Each connected adapter can be used to further extend the desktop or mirror the image shown on the existing display - all without having to open the computer case to install an additional video card.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card
- Add multiple (up to five) monitors / projectors to your computer setup using one USB2DVIE2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Optimal performance at 1440x900 (higher resolutions supported) and ideal for use with 17" to 19" monitors or smaller
- Works with desktop and laptop computers
- No power adapter required, easy installation
- Includes easy to use software that allows for screen rotation, multi-display management and EDID monitor detection for increased compatibility with displays
- Supports the use of DVI to VGA or DVI to HDMI adapters

Technical Specifications

Warranty	2 Years
Memory	16MB SDRAM
Chipset ID	MCT - Trigger 1+
Connector A	1 - USB A (4 pin) Male
Connector B	1 - DVH (29 pin) Female
Supported Resolutions	Widescreen(16/32 bit): 1680x1050, 1440x900, 1280x800, 1280x768 Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
OS Compatibility	Window 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2
Color	Black
Product Length	3.6 in [91 mm]
Product Width	2.1 in [53 mm]
Product Height	0.7 in [18 mm]
Product Weight	3.8 oz [108 g]
System and Cable Requirements	One available USB 2.0 port
Shipping (Package) Weight	0.6 lb [0.3 kg]
Included in Package	1 - USB to DVI Adapter
Included in Package	1 - Driver and Software CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

