


3 ft Mini USB 2.0 Cable - A to Mini B

StarTech ID: USB2HABM3



This high quality USB A to Mini B Cable provides one (4-pin) USB Type A male connector and one Mini B (5-pin) male connector, and can support data high speed USB 2.0 transfer rates of up to 480Mbps.

A high quality replacement cable for connecting your USB Mini-B compatible digital camera (Canon, Sony, Hewlett Packard) to a host computer, this USB A to Mini B cable also delivers a cost-effective way to maximize the file transfer performance of your MP3 player, PDA, or digital camcorder.

Expertly designed and constructed of only top quality materials, the A to Mini B USB 2.0 cable provides pure digital data transfers for sharper, more natural images and sound at higher speeds and is backed by our Lifetime Warranty.

Applications and Solutions

- An ideal replacement USB cable for transferring pictures, videos, MP3 files from your digital camera, digital camcorders, MP3 players, PDA and other portable devices to your laptop or desktop PC

Features

- Gives you the freedom to download more pictures and MP3 files with fast data transfer rates of up to 480 Mbits/sec
- Suitable for a variety of digital cameras, camcorders and portable devices
- The new USB Mini B cable meets USB 2.0 requirements which is 40 times faster than USB 1.0

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - USB A Male
- Connector B: 1 - USB Mini B 5 pin Male
- Color: Gray
- Product Length: 3 ft [0.91 m]
- Carton Quantity: 300
- Shipping (Package) Weight: 0.07 lb [0.03 kg]
- Wire Gauge: 30 AWG
- Length: 3 ft (0.9 m)
- USB Standard: 2.0
- Data Transfer Rate: Up to 480 Mbits/sec
- Compatibility: PC and Mac
- Connectors: Connector 1: 4 pin USB Type A (male)
 - Connector 2: Mini B 5 pin (male)
- **Digital Camera Compatibility:**
- **Canon® PowerShot Digital Camera:**
 - Model # S300 Digital ELPH
 - Model # A20
 - Model # A10
 - Model # DSC-P50
 - Model # DSC-S75
 - Model # DSC-S85
 - Model # MVC-CD200
 - Model # MVC-CD300
 - Model # MVC-FD92
- **Casio® Digital Camera:**

- Model # QV-4000
- **HP® PhotoSmart Digital Camera:**
 - Model # 318
 - Model # 612
 - Model # 715
- **Sony® Cybershot Digital Camera:**
 - Model # DSCP-1
 - Model # DSCP-3
 - Model # DSCP-5
 - Model # DSCP-9
 - Model # DSCP-20
 - Model # DSCP-30
 - Model # DSCP-50
 - Model # DSCP-51
 - Model # DSCS-75
 - Model # DSCS-85
 - Model # DSCF-707
- **Sony® Mavica Digital Camera:**
 - Model # MVC-FD92
 - Model # MVC-CD200
 - Model # MVC-CD300
 - Sony Mini DV DCR-PC110
- **Sony® Digital Camcorder:**
 - Model # DCR TRV17
- **Panasonic® Digital Camera:**
 - Lumix DMC-LC5
 - Lumix DMC-LC40

