

Cubicle Hanging Monitor Mount

Product ID: ARMCBCL



With these cubicle monitor hangers, you can free up desk space by mounting monitors on the partitions between office cubicles. Each hanger can hold a monitor of up to 30" at 20 lb. (9 kg), and it provides both tilt and height adjustments so that your employees can position their displays for maximum comfort.

Create extra desk space and tidy up your cubicles

Without monitors taking up valuable work space, your employees can work more comfortably. These hangers can help you create extra elbow room in smaller work environments such as call centers, freeing up space for additional hardware or physical tasks such as drafting or reading paper documents. They can also help keep employees' workstations tidy by reducing the amount of equipment on their desks.

The cubicle hangers also provide an easy way to clear cable clutter. They feature an integrated cable organizer that neatly tucks cables out of the way.



Work more comfortably

The monitor cubicle mount features easy-to-adjust height and tilt mechanisms to customize the positioning of displays. This helps you create ergonomic work spaces that match each employee's distinct needs. They can adjust the height of their monitors without disrupting their work: simply pull out the height-adjustment pin and slide the monitor to the desired height. The mount allows for 16" of height adjustment. Once they select the desired height, they can tilt their monitors to adjust their viewing angle.

For viewing longer pages or blocks of code without having to scroll down the screen, the cubicle LCD mount also supports simple landscape-to-portrait display rotation.

Hang a monitor on almost any cubicle

The monitor hanger can work with almost any cubicle size. It can fit over various wall sizes ranging from 1.5" to 5.5" in thickness and is recommended for wall heights ranging from 19" to 30" above the desk level. The maximum varies slightly by user height.

The hanger also has a discreet, low-profile design that won't interfere with shelves that are mounted on a cubicle wall or disturb co-workers who are working in an adjacent cubicle. Plus, it's designed to protect the top of the cubicle wall from scratches and marks.



Enjoy hassle-free setups

The monitor mount provides fast and easy installations. Simply select the width, attach the monitor, hang it over the cubicle wall, adjust the height and route the cables.

There's no need to assemble multiple parts, and no need to clamp anything to a desk. The cubicle-wall monitor mount comes with virtually no assembly and can be set up and ready to use in no time.

The ARMCBCL cubicle monitor hanger is backed by a StarTech.com 2-year warranty and free, lifetime technical support.

**Certifications, Reports
and Compatibility**



Applications

- Hang a monitor over a cubicle wall and adjust the height as needed
- Rotate the monitor to portrait orientation for web design and coding

Features

- Optimize desk space by completely removing a monitor from your employee's desk
- Work more comfortably, with hassle-free height and tilt adjustments
- Supports a monitor up to 30" (20 lb. / 9 kg capacity)
- Virtually no assembly required
- Optimized for wall heights ranging from 19" to 30" above the desk level
- Provides 16" in height-adjustment

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Articulating	No
	Mounting Options	Cubicle Wall
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Maximum Display Size	30in
	Mounting Surface Thickness	1.5" (38 mm) to 5.5" (139 mm)
	Weight Capacity (Per Display)	19.9 lb [9 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel, Aluminum and Plastic
	Product Height	18.1 in [460.5 mm]
	Product Length	3.7 in [93 mm]
	Product Weight	28.1 oz [796 g]
	Product Width	4.7 in [120 mm]
Packaging Information	Shipping (Package) Weight	2.6 lb [1.2 kg]
What's in the Box	Included in Package	1 - hanging cubicle monitor mount 1 - small L-bracket 1 - large L-bracket 2 - rubber pads 4 - M4x12 screws 4 - M4x25 screws 4 - spacers 1 - instruction manual

Product appearance and specifications are subject to change without notice.