

## Desk-Mount Monitor Arm - Full Motion Articulating - Slim Profile

Product ID: ARMSLIM



This slim, articulating monitor arm lets you mount a flat-panel display on your desk or table, with dynamic adjustments that make it easy to position your monitor for the perfect viewing angle and optimal comfort. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The versatile monitor arm lets you extend, tilt, pan, swivel and pivot your display with a full range of motion across multiple axes, and features spring-assisted height adjustments for effortless positioning. For viewing longer pages or blocks of code without having to scroll down your screen, the LCD arm also supports simple landscape-to-portrait display rotation.

With a stylish, slim design that looks great and takes up only a small amount of desk space, the monitor arm gives you the flexibility to locate your display as needed while reclaiming valuable workspace on your desk. Mounting your display above the desk surface enables you to adjust your display height, position and viewing angles easily, for an ergonomic work environment.

Supporting 12 - 26" displays up to a maximum weight capacity of 15lbs (7kg), the monitor-mounting arm holds your display with ease, and integrates a cable management channel to keep things neat. For added installation flexibility, the included mounting hardware can either clamp to the side of your desk / table or mount through a grommet hole.

The StarTech.com ARMSLIM monitor arm is backed by a StarTech.com 2-year warranty and free, lifetime technical support.



### Certifications, Reports and Compatibility



### Applications

- Mount a display to the side of your desk or table with a wide range of adjustment capability
- Grommet mount your display through a desk or above a server cabinet and position as needed
- Elevate your display higher above your desk surface for ideal viewing angles
- Rotate displays to portrait orientation for web design and coding

### Features

- Slim, articulating monitor arm with a wide range of motion
- Spring-assisted height adjustment
- TAA compliant for GSA Schedule purchases
- Supports displays from 12 to 26" (15lbs / 7kg capacity)
- 360° rotation around the support post and at the elbow
- +90° / -65° Tilt and 360° Pan
- Maximum arm extension of 23.46in (596mm)
- Includes convertible desk / grommet-mount clamp
- Clamp fits desks up to 4.33in (110mm) thick
- Integrated cable management

<b>Hardware</b>	Warranty	2 Years
	# of Displays Supported	1
	Articulating	Yes
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
<b>Performance</b>	Display Rotation	+/- 90°
	Height Adjustment	Yes
	Maximum Arm Extension	23.5 in [596 mm]
	Maximum Display Size	26in
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 3.93 in. (20 - 100 mm) Grommet Clamp: Table Thickness 0.78 - 1.96 in. (20 - 50 mm) Table Hole for Grommet Mount: 0.39 - 2.36 in. (10 - 60 mm)
	Pan	360°
	Swivel / Pivot	180° around the support post 360° at the elbow
	Tilt	+90° / -65°
	Weight Capacity (Per Display)	15.5 lb [7 kg]
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel and Plastic
	Product Weight	7 lb [3.2 kg]
<b>Packaging Information</b>	Shipping (Package) Weight	9.3 lb [4.2 kg]
<b>What's in the Box</b>	Included in Package	1 - Articulating Monitor Arm
		1 - 2-in-1 Desk / Grommet Clamp
		4 - Thumb Screws
		1 - 6mm Allen Wrench
		1 - 3mm Allen Wrench
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.