


Gooseneck Tablet Holder - Bendable Tablet Arm

Product ID: ARMTBLTUGN



Add flexibility to your workspace, with this gooseneck tablet holder for most 7" to 11" tablets. The desk-mount tablet stand has an adjustable clamp that fits tablets with a width or length of 6.5" to 7.8" (166 to 200 mm) and a maximum tablet thickness of 0.45" (11.5 mm). Mount your tablet width-wise or length-wise, and rotate it 360-degrees. Use it with your Apple iPad, Samsung Galaxy, Microsoft Surface 3 or other tablets.



Flexible and Adjustable Positioning

Place your tablet exactly where you need it and position it to your preferred viewing angle with the flexible 19.7" (500 mm) gooseneck arm, bending 360 degrees in any direction. It tilts, turns and rotates, letting you easily switch between landscape and portrait position.

Installs on Virtually Any Surface

The arm is simple to mount on a desk, counter, tabletop or any other surface, with a thickness of 0.8 to 1.9" (20 to 50 mm). The included clamp holds the arm securely in place. The tablet holder is detachable with quick-swap attachments that let you remove the tablet from the arm and pop it back in as needed.

Hands-Free Use

Install a tablet beside your display for easy reference to documentation, presentations and research. With the gooseneck arm in place, it's easy to integrate a tablet into your work space and keep your hands free to type and swipe. Using a tablet hands-free can be helpful for individuals with mobility challenges.

The TAA Compliant ARMTBLTUGN is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Integrate a tablet into your work space, beside your display
- Quickly detach the tablet and bring it with you to a meeting
- Reference documentation, presentations and research
- Use your tablet without having to hold it

Features

- Fits most 7" to 11" tablets, with tablet width or length of 6.5" to 7.8" (166 to 200 mm) and max tablet thickness: 0.45" (11.5 mm)
- Quickly adjust your tablet's viewing angle with this gooseneck tablet mount (with 19.7" 500 mm bendable arm)
- Flexible gooseneck tablet holder turns, tilts and rotates 360 degree into landscape or portrait position
- Detachable design with quick-swap attachments
- Clamp the tablet mount onto a desk, table or other surface 20 mm to 50 mm thick

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Mounting Options	Desk & Grommet Clamp
	Wallmountable	No
Performance	Display Rotation	360°
	Display Swivel	+90° / - 90°
	Display Tilt	+90° / - 90°
	Height Adjustment	Yes
	Maximum Display Size	11"
	Maximum Tablet Thickness	0.5 in [11.5 mm]
	Minimum Display Size	7"
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 1.96 in. (20 - 50 mm)
	Swivel / Pivot	360° in any direction
Physical Characteristics	Color	Black
	Enclosure Type	Steel and Plastic
	Product Height	3.2 in [82 mm]
	Product Length	19.7 in [50 cm]
	Product Width	7.3 in [18.5 cm]
	Weight of Product	2.2 lb [1 kg]
Packaging Information	Package Height	2.2 in [55 mm]
	Package Length	16.7 in [42.5 cm]
	Package Width	14.1 in [35.8 cm]
	Shipping (Package) Weight	3.2 lb [1.4 kg]
What's in the Box	Included in Package	1 - tablet holder
		1 - gooseneck arm
		1 - clamp
		1 - quick start guide

Product appearance and specifications are subject to change without notice.