

USB 3.0 Front Panel 4 Port Hub – 3.5in or 5.25in Bay

Product ID: 35BAYUSB3S4



The 35BAYUSB3S4 3.5-inch Front Bay to 4-Port USB 3.0 Panel Hub is TAA compliant and turns any available 3.5-inch computer case front bay into a 4-Port USB 3.0 hub.

Using only a single USB connection, this front panel hub adds four easily accessible USB ports to the front of your computer case through a 3.5-inch bay, or through a 5.25-inch bay using the optional [Front Bay Bracket Adapter](#) (BRACKETFDBK) accessory. Each of the added ports is compliant with the USB 3.0 standard which supports up to 5 Gbps of bandwidth (10x faster than the USB 2.0 standard) and up to 900mA of power.

Accessorize with the PEXUSB3S11 PCI Express card to provide an internal USB 3.0 port, so as to keep the external ports free for external devices. Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Expand your system's USB 3.0 capabilities with additional ports for connecting high speed external storage devices
- Add easier to access USB ports to the front of a computer system instead of the rear
- Make use of an internal USB port and unused 3.5" front bay to increase the system's expandability

Features

- TAA Compliant
- Four front accessible USB type-A ports
- Fits into any 3.5" computer case front bay
- SuperSpeed USB 3.0 compliant, supporting data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.0/1.1 specifications and devices
- Provides up to 900mA of power per port
- USB Link LED indicator for each port

Hardware	Warranty	2 Years
	Chipset ID	VIA/VLI - VL811+
	Fast-Charge Port(s)	No
	Interface	USB 3.0
	Ports	4
	USB-C Device Port(s)	No
	USB-C Host Connection	No
Performance	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	External Ports	4 - USB Type-A (9 pin) USB 3.0 Female
	Internal Ports	1 - SATA Power (15 pin) Plug 1 - USB Type-B (9 pin) USB 3.0 Female
Software	OS Compatibility	OS Independent; No additional drivers or software required
Special Notes / Requirements	System and Cable Requirements	Available 3.5 inch front bay
		Available USB 3.0 type A port
Indicators	LED Indicators	4 - USB Device Link (Green)
Power	Power Source	USB-Powered
Environmental	Humidity	20% ~ 80% RH
	Operating Temperature	5°C to 50°C (41°F to 122°F)
	Storage Temperature	-25°C to 70°C (-13°F to 158°F)
Physical Characteristics	Color	Black
	Enclosure Type	Plastic
	Form Factor	Drive Bay
	Product Height	1 in [25 mm]
	Product Length	4.7 in [120 mm]
	Product Weight	3.5 oz [100 g]
	Product Width	3.9 in [100 mm]
Packaging Information	Shipping (Package) Weight	7.6 oz [214 g]
What's in the Box	Included in Package	1 - 3.5" Front Panel
		1 - USB 3.0 Cable
		1 - Mounting Screw Kit

Product appearance and specifications are subject to change without notice.