

Monitor Wall Mount - Aluminum

Product ID: ARMWALL



Wall-mount your computer monitor or flat-screen TV to free up space on your desk or table. This monitor wall mount supports displays up to 27". It swivels and tilts to enable you to adjust the angle of your screen and provide viewing flexibility.

Save space by wall-mounting your flat-panel display

The monitor wall mount helps you save space on your desk or table surface, by letting you securely wall-mount a computer monitor or LED / LCD TV from 13" to 27" (330 to 686 mm) in size and up to 33 lb. (15kg) in weight. It's ideal for many different applications, including business meeting rooms, healthcare or financial settings. The monitor wall mount works well in office settings or workspaces that back against a wall.

Adjust your screen position with ease

The monitor wall mount makes it easy to change your screen position, so you can work more comfortably. It swivels +45° / - 45°, enabling you to move your screen easily to the left or right. It also tilts freely +45° / - 45°, which makes it easy to adjust the angle of your display up or down.

Easy installation

The aluminum monitor wall mount features slide-in wall plate construction for easy installation. To help keep your work area free of clutter, the monitor arm also features a cable clip that keep your cables neatly out of sight.

The ARMWALL is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Free up desk or table space in business, commercial, industrial or office settings
- Wall mount a computer monitor or flat-screen TV in meeting rooms, healthcare or financial settings
- Ideal in office settings or work spaces that back against a wall
- Create space and work more comfortably in home office settings

Features

- Mount your monitor or flat-screen TV on a wall to save space and easily share your screen
- Supports a 13" - 27" monitor up to 33 lb. (15 kg)
- Swivels +45° / - 45° to provide viewing flexibility
- Tilts freely +45° / - 45° allowing easy angle adjustment up or down
- Easy installation with slide-in wall plate construction
- Supports VESA mount compliant monitors: 50x50, 75x75, 100x100
- Cable management

| | | |
|---------------------------------|-------------------------------|---------------------------------|
| Hardware | Warranty | 2 Years |
| | # of Displays Supported | 1 |
| | Articulating | No |
| | Cable Management | Yes |
| | Mounting Options | Wall-Mount |
| | VESA Hole Pattern(s) | 50x50 75x75 mm 100x100 mm |
| Performance | Display Rotation | 0° |
| | Height Adjustment | No |
| | Maximum Display Size | 27in |
| | Minimum Display Size | 13" |
| | Swivel / Pivot | +45° / - 45° |
| | Tilt | + 45° / - 45° |
| | Weight Capacity (Per Display) | 33.2 lb [15 kg] |
| Physical Characteristics | Color | Black |
| | Enclosure Type | Aluminum |
| | Product Height | 21.7 in [550 mm] |
| | Product Length | 4.5 in [114 mm] |
| | Product Weight | 9.6 oz [272 g] |
| | Product Width | 4.5 in [114 mm] |
| Packaging Information | Shipping (Package) Weight | 15.1 oz [427 g] |
| What's in the Box | Included in Package | 1 - display mount |
| | | 1 - hex key |
| | | 1 - wrench |
| | | 4 - M4x14 mm screws |
| | | 4 - M5x14 mm screws |
| | | 4 - washers |
| | | 2 - screws |
| | | 2 - wall screws |

1 - instruction manual

Product appearance and specifications are subject to change without notice.