

Dual-Monitor Stand - Vertical

Product ID: ARMBARDUOV



This sturdy and sleek dual-monitor stand raises two displays off the surface of your desk or table, to save space while increasing your productivity. With its steel construction, the freestanding monitor stand securely holds two monitors, each up to 27", stacked vertically.



Configure your displays to enhance productivity

The dual-monitor stand holds two displays, one above the other, in a vertical configuration. You can work more comfortably, reducing neck and eye strain without having to look side to side when comparing files or reviewing reference material on your screens. It's ideal for numerous applications including web design, coding, creating and reviewing files, and many others. The monitor mount saves valuable desk space and lets you work clutter-free, which is a welcome addition in numerous office environments including business, healthcare and financial settings. You can adjust the height of the monitors as needed, along the 32.2" (818 mm) pole.

Adjust your screens to the ideal position

The monitor stand enables smooth, effortless $+45^{\circ}/-45^{\circ}$ tilt and $+45^{\circ}/-45^{\circ}$ swivel, making it easy to reduce glare and find the perfect viewing angle. It can also rotate a full 360° giving you the flexibility of portrait or landscape viewing.

Rugged steel design

The heavy-duty steel monitor stand holds your monitors securely in place, to protect your investment and provide long-lasting stability. The dual-monitor stand supports two displays 13" to 27" (330 to 686 mm) in size and 22.1 lb. (10 kg) in weight per monitor. The surface finish features a powder coating to help resist scratches.

For easier mounting, the VESA mount features notches that let you pre-set the mounting screw, then slide the monitor into place and tighten the screw. To help keep your work area free of clutter, the monitor stand also features cable clips that keep your cables neatly out of sight.

The ARMBARDUOV is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Stack your displays one on top of the other, ideal for web design or coding
- Increase your comfort when working on two screens to create files or compare documents
- Enhance your productivity in office settings including business, healthcare, financial and real estate
- Save space in your home office

Features

- Mount two monitors vertically to save space and increase your comfort
- Freestanding monitor stand supports two displays up to 27" (686 mm) in size and 22.1 lb. (10 kg) in weight per monitor
- Heavy-duty steel construction
- The height of the monitors can be adjusted along the 32.2" (818 mm) pole
- Adjust your screen angle easily with +45°/-45° tilt and +45°/-45° swivel
- Full 360° rotation
- Cable management

Hardware	Warranty	2 Years
	# of Displays Supported	2
	Mounting Options	Desktop Stand
	Orientation	Vertical
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Display Rotation	360°
	Maximum Display Size	27in
	Minimum Display Size	13"
	Swivel / Pivot	+45° / -45°
	Tilt	+ 45° / - 45°
	Weight Capacity (Per Display)	22.1 lb [10 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	32.2 in [818 mm]
	Product Length	12.4 in [316 mm]
	Product Weight	8.9 lb [4 kg]
	Product Width	17.1 in [434 mm]
Packaging Information	Shipping (Package) Weight	10.7 lb [4.8 kg]
What's in the Box	Included in Package	1 - lower pole 1 - upper pole 1 - baseplate 2 - VESA monitor mounts 1 - pole connector 2 - cable-management clips 1 - cap 1 - 3 mm hex key 1 - 5 mm hex key 1 - 6 mm hex key

8 - M4x12 mm screws

8 - M5x12 mm screws

8 - washers

1 - instruction manual

Product appearance and specifications are subject to change without notice.