

## Cubicle Monitor Mount - With Micro-Adjustment

Product ID: ARMCBCLB



Free up valuable desk space in your cubicle workstation with this cubicle monitor mount. It lets you mount a monitor on your cubicle wall to keep your work area more organized, comfortable and productive.

### Heavy-Duty Steel

The cubicle monitor hanger, made of steel with a metallic silver finish, securely supports a 17" to 32" VESA mount monitor, with a maximum weight of 17.6 lb. (8 kg).

### Free Up Desk Space

The cubicle wall monitor mount helps you free up surface area in your workspace, and keeps cables neat with integrated cable management.

### Adjustable for Ideal Viewing

Adjust your screen height quickly, by pulling the lever while sliding the monitor to the desired height. Up to 12" of height adjustment accommodates a wide range of users.

For customized viewing, tilt your monitor +/-10 degrees and swivel +/-10 degrees. The cubicle monitor mount also rotates +/-180 degrees, for landscape or portrait positioning.

### **Scalable Solution**

Customize your work area by hanging multiple monitors, using several cubicle monitor hangers to create a multi-monitor workstation. The micro-adjustment feature lets you align your monitors in perfect unison. Plus, angle your monitors for optimum viewing.

### **Virtually No Assembly**

The cubicle-wall monitor mount is easy to set up. The monitor mount works in most cubicles, with wall sizes from 1.5" to 3.5" in thickness. It's optimized for wall heights ranging from 19" to 30" above the desk surface.

ARMCBLB is backed by a StarTech.com 2-year warranty and free, lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Maximize desk space in cubicle-style work environments
- Rotate the monitors to portrait orientation, ideal for web design and coding
- Hang multiple monitors over a cubicle wall to create a multi-monitor workstation

### Features

- Maximize desk space with this cubicle monitor mount for 17" to 32" monitors
- Heavy-duty steel mount supports up to 17.6 lb. (8 kg) weight capacity
- Up to 12" height-adjustment range, plus tilt, swivel, and rotation
- Hang multiple monitors and align them with micro-adjustment
- Adjustable cubicle monitor hanger fits most standard cubicle walls

<b>Hardware</b>	Warranty	0 Years
	# of Displays Supported	1
	Articulating	No
	Mounting Options	Cubicle Wall
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
<b>Performance</b>	Display Rotation	+180° / -180°
	Display Tilt	+10° / -10°
	Maximum Display Size	32in
	Mounting Surface Thickness	1.5" (38 mm) to 5.5" (139 mm)
	Swivel / Pivot	+10° / -10°
	Weight Capacity (Per Display)	17.7 lb [8 kg]
<b>Physical Characteristics</b>	Color	Silver
	Enclosure Type	Steel and Plastic
	Product Height	136.000
	Product Length	510.000
	Product Width	136.000
	Weight of Product	1600.000
<b>Packaging Information</b>	Package Height	0.000
	Package Length	0.000
	Package Width	0.000
	Shipping (Package) Weight	0 lb [0 kg]
<b>What's in the Box</b>	Included in Package	1 - Cubicle Mount 1 - EVA Foam Pad 1 - Hex Key 4 - Washers 4 - Spacers 4 - M4x12 mm Screws 4 - M4x16 mm Screws

4 - M5x12 mm Screws

4 - M5x16 mm Screws

1 - User Manual

---

Product appearance and specifications are subject to change without notice.