

Desk-Mount Quad-Monitor Arm - Articulating - Heavy Duty Steel

Product ID: ARMQUAD



Free up valuable space by mounting four monitors on one base, to suspend your monitors above the surface of your desk, workstation or table. This sturdy desk-mount quad-monitor arm is constructed of heavy-duty steel and will hold all four displays securely in place to create an impressive and productive workspace.



Enhance your productivity while saving space

Create the ultimate workstation by mounting four monitors on one base that attaches securely to your desk, table or other surface. You can view multiple screens at the same time to work more efficiently while freeing up space.

The quad-monitor arm offers enhanced productivity in numerous office and commercial applications, such as banking and finance, letting you compare documents and analyze data more effectively. It's also ideal for software developers, programmers, CAD designers, and many other professionals. You can also create engaging digital signage displays to communicate with your clients or employees.

Rugged Steel Design

With its heavy-duty solid steel construction, the quad-monitor mount securely holds your monitors and helps to ensure long-lasting performance. Each monitor arm supports a flat-panel display from 13" to 27" (330 to 686 mm) in size and up to 17.6 lb. (8 kg) in weight.

Adjust your monitors for ideal viewing

You can adjust the position and angle of your monitors for comfortable viewing, with +30° to -30° swivel and tilt. The quad-monitor mount enables smooth and effortless tilting, which makes it easy to reduce glare and find the ideal viewing angle. For precise alignment, the monitor arm offers micro adjustments that enable you to perfectly line up your displays.

Easy installation

The monitor mount supports four VESA mount compliant monitors and it's easy to install using the desk clamp or grommet mount. To keep your cables neatly tucked away, the quad-monitor arm features cable management clips that help to keep your workstation tidy.

The ARMQUAD is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount four monitors to enhance data analysis in commercial environments such as banking and finance, and control centers
- Increase productivity, ideal for software developers, programmers and CAD designers
- Create impressive digital signage displays

Features

- Mount four monitors (2x2) off of your desk or table surface to free up space
- Solid steel construction holds monitors securely and level, with no sag
- Each arm supports a 13" to 27" (330 to 686 mm) monitor weighing up to 17.6 lb. (8 kg)
- Micro adjustment of monitors for level viewing
- Full 360° rotation for portrait or landscape orientation
- Swivels and tilts +30° to -30° to adjust your viewing angle
- Desk clamp and grommet mount with cable-management clips

Hardware	Warranty	2 Years
	# of Displays Supported	4
	Articulating	No
	Cable Management	Yes
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Display Rotation	360°
	Maximum Display Size	27in
	Maximum Height	28.5 in [723 mm]
	Minimum Display Size	13"
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Table Hole for Grommet Mount: 0.41 - 1.96 in. (10.5 - 50 mm)
	Swivel / Pivot	+30° / -30°
	Tilt	+ 30° / - 30°
	Weight Capacity (Per Display)	17.7 lb [8 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	32.6 in [828 mm]
	Product Length	4.5 in [115 mm]
	Product Weight	16.7 lb [7.6 kg]
	Product Width	32.9 in [835 mm]
Packaging Information	Shipping (Package) Weight	20.4 lb [9.2 kg]
What's in the Box	Included in Package	4 - monitor arms 4 - VESA monitor mounts 1 - lower pole 1 - upper pole 1 - pole connector

- 4 - cable-management clips
- 4 - end caps
- 4 - thumbscrews
- 1 - desk clamp
- 1 - 3 mm hex key
- 1 - 5 mm hex key
- 16 - M4x14 mm screws
- 16 - M5x14 mm screws
- 16 - washers
- 1 - grommet collar
- 1 - grommet plate
- 5 - rubber pads
- 1 - instruction manual

Product appearance and specifications are subject to change without notice.