


## Quad-Monitor Stand - Articulating - Steel & Aluminum

Product ID: ARMQUADSS



Boost productivity and customize your workspace with this quad-monitor stand, suspending four monitors above your desk. Enjoy optimum viewing with four articulating monitor arms, providing a wide range of motion. The free-standing base gives you flexibility in placing your setup within your workspace.



## Designed for Productivity

Constructed of aluminum and steel, the heavy-duty four-monitor stand lets you set up your workspace for optimum productivity. The monitor stand supports four VESA mount (75x75, 100x100) monitors up to 32" each, with a maximum weight capacity of up to 17.6 lb./8 kg per display.

## Create a More Ergonomic Workspace

Create a multi-monitor workstation that works best for you. Take advantage of four-screen efficiency for financial analysis, web coding, video editing or many other applications. Customize your setup by adjusting your display height, position and viewing angles for an ergonomic workspace. The swiveling arms provide maximum viewing flexibility.

## Height-Adjustable Monitor Mount

Place your monitors at the ideal height. Simply adjust the display height along the 34" (864 mm) pole. Align your monitors with the micro-adjustment feature.

## Enjoy Optimum Viewing

The four-screen monitor stand lets you extend the articulating arms up to 16.6" (42.2 cm) to position your monitors in the ideal position. Tilt your monitors +90/-40 degrees and swivel 360 degrees. Rotate your displays 360 degrees for portrait or landscape viewing.

## Keep Cables Out of View

Neatly route your cables with the cable-management channels.

ARMQUADSS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Create a more ergonomic workspace in office, commercial or institutional environments
- Utilize four-screen efficiency for financial analysis, web coding, video editing or many other applications
- Enhance productivity and free up space in your home office workstation

### Features

- Save space by mounting four VESA mount monitors (75x75, 100x100) up to 32" each, on a free-standing base
- Heavy-duty quad-monitor stand supports four monitors up to 17.6 lb./8 kg per display
- Four articulating arms extend up to 16.6" (42.2 cm) and provide a wide range of motion
- Height adjustable along the 34" (864 mm) pole
- Enjoy optimum viewing with 360-degree swivel, +90/-40 degree tilt and 360 degree screen rotation

<b>Hardware</b>	Warranty	5 Years
	# of Displays Supported	4
	Articulating	Yes
	Cable Management	Yes
	Mounting Options	Desktop Stand
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
<b>Performance</b>	Display Pan	360°
	Display Rotation	360°
	Display Tilt	+90° / -40°
	Height Adjustment	Yes
	Maximum Arm Extension	16.6 in [422 mm]
	Maximum Display Size	32in
	Weight Capacity (Per Display)	17.7 lb [8 kg]
<b>Physical Characteristics</b>	Product Height	4.9 in [12.5 cm]
	Product Length	21.8 in [55.3 cm]
	Product Width	13.7 in [34.8 cm]
	Weight of Product	18.4 lb [8.3 kg]
<b>Packaging Information</b>	Package Height	0 in [0 cm]
	Package Length	0 in [0 cm]
	Package Width	0 in [0 cm]
	Shipping (Package) Weight	0 lb [0 kg]
<b>What's in the Box</b>	Included in Package	4 - Swivel Arms 4 - VESA Mounts 2 - Shoulders 1 - Upper Pole 1 - Lower Pole 1 - Pole Connector 1 - Base 2 - Cable-Management Clips

16 - M4x16 Screws

16 - M4x12 Screws

16 - M5x16 Screws

16 - M5x12 Screws

16 - M4x20 Screws

16 - M5x20 Screws

32 - Spacers

16 - Washers

1 - 3mm Hex Key

1 - 6mm Hex Key

1 - User Manual

---

Product appearance and specifications are subject to change without notice.