

4x 2.5" SSD/HDD Mounting Bracket with Cooling Fan

Product ID: BRACKET425F



Increase the performance and data storage capacity of your desktop computer or enhance your server room storage, with this 4-drive mounting bracket kit for 2.5" solid-state drives or hard drives.

Maximize the internal data storage of your computer

This drive-mounting bracket lets you add four 2.5" SSDs or HDDs into two 5.25" front bays of your computer or server, allowing you to enhance your data storage capacity. The mounting brackets supports a wide range of 2.5" SSDs/HDDs from 5 to 15 mm in height.

Built-in cooling helps prevent damaging heat build-up

A large built-in fan keeps air moving to dissipate heat build-up, and ensure optimum operating temperatures. Protecting against excessive heat build-up maximizes the life of your drives. The fan also features a dust filter making the mounting bracket ideal for industrial or corporate environments.

Designed for dependable performance

Engineered with steel framing, the mounting bracket is designed for dependable performance and durability. BRACKET425F is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add the performance and storage capacity of four 2.5" SSD/HDDs, installed into two unused 5.25" bays in your desktop computer or server
- Cooling fan with dust filter makes the mounting bracket ideal for industrial and corporate environments
- Repurpose unused laptop hard drives to work with your desktop computer

Features

- Mount four SSDs/HDDs into two front bays (5.25") of your desktop computer or server
- Supports 2.5" SSD/HDDs from 5 - 15 mm
- Durable mounting bracket with steel framing
- Cooling fan with filter helps to ensure optimum operating temperature

	Warranty	2 Years
Physical Characteristics	UL Flammability Rating	UL94-VO
Hardware	Compatible Drive Types	SATA & IDE
	Drive Installation	Fixed
	Drive Size	2.5in
	Fan Bearing Type	Dual Ball Bearing
	Fan(s)	Yes
	Fans	1 - 80 mm
	Number of 2.5 inch bays	4
	Number of Drives	4
	Supported Drive Height(s)	5mm 7mm 9.5mm 12.5mm 15mm
Performance	MTBF	50000 hours
Connector(s)	Host Connectors	1 - Molex (4 pin, PWM)
Physical Characteristics	Color	Black
	Enclosure Type	Steel and Plastic
	Max Drive Height	0.6 in [15 mm]
	Product Height	3.3 in [85 mm]
	Product Length	6.4 in [162 mm]
	Product Weight	18.4 oz [520 g]
	Product Width	5.9 in [150 mm]
Packaging Information	Shipping (Package) Weight	22.2 oz [628 g]
What's in the Box	Included in Package	1 - SSD/HDD mounting bracket with fan 1 - mounting screws pack 1 - quick start guide

Product appearance and specifications are subject to change without notice.