

Sit-Stand Monitor Arm

Product ID: ARMSTSCP1



This sit-stand monitor arm transforms your desk or tabletop into an ergonomic workstation. The monitor arm features a keyboard tray and easy height adjustment that lets you alternate between sitting and standing, without interrupting your workflow. Move your workstation up or down, left or right, to meet your needs.

Adjust the height with one smooth motion

Adjust your position, with one smooth motion. Simply lift the work surface up to 17.7" (450 mm), to elevate both your monitor and keyboard. You can adjust the tension to your own preference. The monitor mount has a separate height adjustment of up to 4.9" (124 mm) along the column.

Optimum adjustability

This sit-stand monitor arm supports one monitor up to 24". The swing arm swivels from -90° to 90° and tilts from -30° to 65° for ideal viewing. The VESA mount also rotates up to 360° for portrait or landscape orientation.

Ample working space

The monitor arm features a large keyboard tray (17.68 x 8.15"/ 449 x 207 mm) with ample working space. A slide-out tray (8.5 x 8.4" / 217 x 213 mm) holds your mouse, on the left or right.

To make the most of your workspace, you can tuck the monitor arm away when it's not in use, to free up space. The keyboard tray also folds up to 90°.

Flexible installation

The compact sit-stand monitor arm features a grommet assembly and desk-clamp option, to fit easily into your workspace, including space-limited corners.

The ARMSTSCP1 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create a single monitor sit-stand workstation with versatile applications in business settings, corporate and institutional environments, or the home office
- Provides a cost-effective solution for enhancing ergonomics by using existing desks and work spaces, even in confined areas
- Mount a display to your current desk, counter or tabletop, with tilt, swivel and height adjustment capabilities

Features

- Turn your desk into an ergonomic workstation with this sit-stand monitor arm, for one monitor up to 24"
- The work surface has a height adjustment of up to 17.7" (450 mm)
- Monitor mount has a separate height adjustment of up to 4.9" (124 mm) along the column
- Adjust your monitor for ideal viewing, with -90° to 90° swivel and -5° to 35° tilt
- Viewing distance: 16.1" (408.7 mm)
- Rotates 360° for landscape or portrait viewing
- Built-in cable-management keeps your workstation well organized
- The arm tucks away and the keyboard tray folds up to 90°, saving space when not in use
- Clamp and grommet base options for flexible installation options, including space-limited areas such as desk corners or rear sides
- 100x100 mm, 75x75 mm VESA mount compatible
- TAA compliant

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Cable Management	Yes
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	100x100 mm 75x75 mm
Performance	Display Rotation	360°
	Height Adjustment	Yes
	Maximum Display Size	24in
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.31 - 1.96 in. (8 - 50 mm) Grommet Clamp: Table Thickness 0.31 - 1.96 in. (8 - 50 mm) Table Hole for Grommet Mount: 0.33 - 2.55 in. (8.5 - 65 mm)
	Swivel / Pivot	+90° / -90°
	Tilt	+35° / -5°
	Weight capacity of monitor arm	17.6 lb. (8 kg) Weight capacity of keyboard tray with grommet mount: 5.6 lb. (2.5 kg) Weight capacity of keyboard tray with desk clamp: 3.3 lb. (1.5 kg)
Physical Characteristics	Color	Black
	Enclosure Type	Steel, Aluminum and Plastic
	Product Height	40.2 in [1020 mm]
	Product Length	26.2 in [666 mm]
	Product Weight	25.2 lb [11.4 kg]
	Product Width	45.3 in [1150 mm]
Packaging Information	Shipping (Package) Weight	27.4 lb [12.4 kg]
What's in the Box	Included in Package	1 - monitor arm 1 - column 1 - keyboard tray 1 - keyboard tray cap 1 - base 1 - VESA monitor mount

- 1 - plastic washer
- 1 - metal washer
- 1 - M8x20 mm screw
- 2 - M6x25 mm screws
- 4 - M6x12 mm screws
- 3 - M6x10 mm screws
- 1 - M6x8 mm screw
- 4 - M4x10 mm screws
- 4 - base screws
- 1 - 2.5 mm hex key
- 1 - 5 mm hex key
- 1 - 6 mm hex key
- 2 - adhesive strip
- 1 - socket driver
- 1 - base pad
- 1 - base plate
- 1 - M8x65 mm screw
- 1 - grommet plate
- 4 - clamp screws
- 1 - clamp L bracket
- 1 - clamp screw assembly
- 1 - instruction manual

Product appearance and specifications are subject to change without notice.