

Wall-Mount Monitor Arm - Single Swivel

Product ID: ARMWALLS



Wall-mount your computer monitor or flat-screen TV to free up space on your desk or table. This wall-mount monitor arm supports flat-panel displays up to 27" and provides 7.7" (195 mm) arm extension allowing versatile screen adjustment. The pivoting arm swivels +90° / - 90° and tilts to provide maximum viewing flexibility.

Save space by wall-mounting your flat-panel display

This monitor arm helps you save space on your desk or table surface, by letting you securely wall-mount a computer monitor or LED / LCD TV from 13" to 27" (330 to 686 mm) in size and up to 33 lb. (15kg) in weight. It's ideal for many different applications, including business, healthcare or financial settings, where you may want to share your screen with patients, clients, or other visitors. The wall-mount monitor arm also works well in office settings or workspaces that back against a wall.

Adjust your screen position with ease

The monitor arm extends 7.7" (195 mm), making it easy to change your screen position, so you can work more comfortably or share your screen with others. The adjustable single-swivel mount offers a full +90° / - 90° swivel, to move your screen easily to the left or right, to share your screen with maximum viewing flexibility. It tilts freely +45° / - 45°, allowing easy angle adjustment up or down to share your display, while collaborating with team members.

Easy installation

The aluminum wall-mount monitor arm features slide-in wall plate construction for easy installation. To help keep your work area free of clutter, the monitor arm also features a cable clip that keep your cables neatly out of sight.

The ARMWALLS is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Free up desk or table space in business, commercial, industrial or office settings
- Share your monitor with clients, for easy collaboration in office settings such as healthcare, financial or real estate
- Create space in home office settings

Features

- Mount your monitor or flat-screen TV on a wall to save space and easily share your screen
- Supports a 13" - 27" monitor or TV up to 33 lb. (15 kg)
- Arm extends 7.7" (195 mm)
- Pivoting arm with +90° / - 90° swivel to provide maximum viewing flexibility
- Tilts freely +45° / - 45°, allowing easy angle adjustment up or down
- Easy installation with slide-in wall plate construction
- Supports VESA mount compliant monitors: 75x75, 100x100
- Cable management

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Articulating	No
	Cable Management	Yes
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
Performance	Display Rotation	0°
	Height Adjustment	No
	Maximum Arm Extension	7.7 in [195 mm]
	Maximum Display Size	27in
	Minimum Display Size	13"
	Swivel / Pivot	+90° / - 90°
	Tilt	+ 45° / - 45°
	Weight Capacity (Per Display)	33.2 lb [15 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Aluminum
	Product Height	4.7 in [119 mm]
	Product Length	7.7 in [195 mm]
	Product Weight	1.1 lb [0.5 kg]
	Product Width	6.1 in [154 mm]
Packaging Information	Shipping (Package) Weight	1.7 lb [0.8 kg]
What's in the Box	Included in Package	1 - display arm
		1 - mounting plate
		1 - 2.5 mm hex key
		1 - 4 mm hex key
		1 - 5 mm hex key
		1 - set screw
		4 - M4x14 mm screws
		4 - M5x14 mm screws

2 - screws

2 - wall screws

1 - instruction manual

Product appearance and specifications are subject to change without notice.