

## Conference Table Connectivity Box for A/V - 4K

Product ID: BOX4HDECP2



This conference table connectivity box for A/V installs in your table or lectern to provide A/V, networking, and USB charging connectivity in your boardroom, auditorium, or classroom. The box makes it easy to connect HDMI, DisplayPort and VGA laptops to your room's large HDMI display, and provides LAN and USB power connectivity for charging USB devices. The box also provides some boardroom cable management by hiding connectivity cables in your table.

### Collaborate Easily Using the Big Screen

The table box enables presenters in your conference room to easily share their laptop screen on the room's large display or projector, with supported resolutions up to 4K 30Hz.

To share video from virtually any laptop, the table box supports HDMI, VGA and DisplayPort inputs and automatically outputs the most recently connected input to the HDMI display.

### Provide Convenient USB Charging and Wired Network Connectivity

Enabling visitors in your conference room to charge their iPhone, iPad, smartphone, or tablet, the table box features three USB charge ports. Plus, the box features an Ethernet pass-through port to provide secure wired network connectivity in rooms where Wi-Fi® isn't available.

### **Add Style and Technological Sophistication to Any Room**

The boardroom interconnect box has an aluminum finish that complements your space. The hideaway panel eliminates clutter by discreetly covering the connection ports when they're not in use.

TAA compliant BOX4HDECP2 is backed by a 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Install in tables or podiums
- Use for presenting and video conferencing
- Share video to collaborate in office environments
- Share video conference software to your entire room

### Features

- Easily collaborate by connecting your HDMI, VGA or DisplayPort laptop to your conference room's HDMI display, from a single access point
- Charge your phone or tablet, with three accessible USB charge ports
- Add style and technological sophistication to your conference room or auditorium by building an A/V connectivity box into your table with a pop-up panel that hides ports when they're not in use
- Provide secure, wired network connectivity in your boardroom table with Ethernet pass-through
- Quickly switch between which laptop screen is shared with automatic A/V switching
- TAA compliant

<b>Hardware</b>	Warranty	2 Years
	Active or Passive Adapter	Active
		Passive
	Audio	Yes
	AV Input	VGA
		3.5 mm Audio
		HDMI
		DisplayPort
AV Output	HDMI	
USB Pass-Through	No	
<b>Performance</b>	Aspect Ratio	16:9
	Maximum Analog Resolutions	1920 x 1200 60Hz
	Maximum Cable Length	50 ft [15.2 m]
	Maximum Digital Resolutions	3840x2160 (4K) 30Hz
	Supported Resolutions	3840x2160 (4K) 30Hz (HDMI and DP Inputs Only)
		2560x1600 60Hz (HDMI and DP Inputs Only)
		1920x1200 60Hz (Maximum VGA Input)
		1920x1080 (1080p) 60Hz
1280x720 (720p) 60Hz		
	**Lower resolutions and refresh rates, not stated but below the maximum, may also be supported	
Video Revision	HDMI 1.4	
	DisplayPort 1.2	
Wide Screen Supported	Yes	
<b>Connector(s)</b>	Connector A	1 - HDMI (19 pin) Female Input
		1 - VGA (15 pin, High Density D-Sub) Female Input
		1 - 3.5 mm Mini-Jack (3 Position) Female Input
		1 - RJ-45 Female
		3 - USB Type-A (4 pin) USB 2.0 Female
		1 - DisplayPort (20 pin) Female Input
	Connector B	1 - HDMI (19 pin) Female Output
		1 - RJ-45 Female

<b>Special Notes / Requirements</b>	<b>Note</b>	VGA (Input) to HDMI (Output) - HDMI Output Port is Active DisplayPort (Input) to HDMI (Output) - HDMI Output Port is Active HDMI (Input) to HDMI (Output) - HDMI Output Port is Passive
<b>Power</b>	Input Voltage	100 ~ 240 AC
	Output Current	2A
	Output Voltage	12 DC
	Plug Type	N
	Power Consumption (In Watts)	24
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	10% to 85% (non-condensing)
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Color	Silver
	Product Height	3.9 in [100 mm]
	Product Length	6.7 in [170 mm]
	Product Weight	2.5 lb [1.1 kg]
	Product Width	3.9 in [100 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	4.1 lb [1.9 kg]
<b>What's in the Box</b>	Included in Package	1 - conference table box 1 - universal power adapter (NA/JP, EU, UK, ANZ) 1 - die cut outline 2 - mounting brackets 1 - cable tie bracket 2 - cable tie bracket screws 1 - quick-start guide

Product appearance and specifications are subject to change without notice.