

Vented 1U Rack Shelf - 16 in. Deep

Product ID: CABSHELF116V



This 1U rack shelf lets you add 16 in. of flat storage space to any EIA-310 compliant server rack or cabinet. The shelf is vented to improve air flow and help lower temperatures in your rack.

Ensure your equipment is secure

The durable fixed-rack shelf can hold up to 20 kg (44 lbs.) of equipment and is constructed using SPCC commercial-grade cold-rolled steel.

Make the most of your available space

The 1U cantilever shelf lets you optimize your working space by giving you the ability to mount equipment to your rack instead of taking up desk or floor space. It's perfect for your SOHO (small office, home office) environment, server room or any other location with limited space available.

Customize your setup

You can install the 1U vented rack shelf in your rack at any height, giving you a stable surface for placing equipment that's un-mountable or storing your tools.

The CABSHELF116V is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Supply additional storage space for mission-critical hardware and non-rackmount equipment

Features

- Improve airflow in your cabinet or rack with a vented shelf
- Ensure your equipment or tools are secure with heavy-duty steel construction
- Save space in your office or server room by placing non-rackmount IT or AV equipment on your rack
- Hassle-free compatibility with EIA-310 compliance
- Installs into 1U of rack space
- EIA-310 compliant
- 16 in. shelf

Hardware	Warranty	Lifetime
	Additional Required Tools	Phillips Screwdriver
	Adjustable Mounting Rails	No
	Cable Management	No
	Frame Type	Steel
	Industry Standards	EIA-310-D
	Mounting Options	Front Mount (Front Only)
	Number and Type of Included Cage Nuts	4 - M6
	Tools Included	No
U Height	1U	
Performance	Weight Capacity (Stationary)	44.2 lb [20 kg]
Special Notes / Requirements	Note	Includes 4x C-cup washers
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Internal Width	17.2 in [436 mm]
	Product Height	1.7 in [44.5 mm]
	Product Length	15.8 in [401 mm]
	Product Weight	6.8 lb [3.1 kg]
	Product Width	19 in [482.6 mm]
	Rail Thickness	0.1 in [2.3 mm]
Packaging Information	Shipping (Package) Weight	8.2 lb [3.7 kg]
What's in the Box	Included in Package	1 - 1U fixed shelf
		4 - cage nuts
		4 - mounting screws

Product appearance and specifications are subject to change without notice.