

## USB-C to HDMI Adapter - with Presentation Mode Switch - 4K 60Hz

Product ID: CDP2HD4K60SA



This is no ordinary video adapter. Yes, it enables you to connect the USB-C™ port on your computer to an HDMI® display or projector, but it also features a unique Presentation Mode switch. When you turn on this switch, the adapter prevents your computer from launching its screen saver, going to sleep or entering power save mode. The adapter ensures that your screen will always stay on, making it the perfect USB-C video adapter for any presentation or meeting.

## Keep your audience engaged with your presentation

When you deliver a presentation, your goal is to engage with your audience, not your computer. But, if you don't move your mouse soon enough, or change your power settings, your screen goes black due to inactivity while you're addressing the audience. This can be a major distraction when you're trying to focus on the message you're communicating.

This adapter prevents screen disruptions with Presentation Mode, a unique feature that automatically initiates occasional cursor movement to prevent your computer's power settings from interrupting your presentation. It's perfect for sharing websites, drawings, spreadsheets, PDFs or slide shows during your meeting.



## Turn Presentation Mode on or off

You can turn Presentation Mode on or off depending on your application. Turn it on when you're in the boardroom and want your screen to stay on, and turn it off when you're using the adapter at your workspace or office hot desk, to enable your computer's original power settings to take effect. Using the toggle switch is easy, and saves you the hassle of constantly making adjustments in your operating system settings.



## Hassle-free setup and operation on Mac and PC

To ensure easy operation and installation, this unique adapter is natively supported on Windows® and Mac computers. It's easy to connect the adapter using the versatile USB Type-C™ port on your computer. The reversible USB-C connector means you will always plug it in correctly on your first try, which saves you the hassle and distraction of repeatedly attempting to connect your laptop to a display or projector.

## Supports 4K resolution at 60Hz

This adapter lets you harness the video capabilities that are built into your computer's USB Type-C connection, to deliver astonishing UHD 4K 60Hz resolution to your HDMI 2.0 display. This makes it easier for you to multitask while you work on the most resource-demanding applications imaginable.

With this adapter, you can achieve an output resolution of up to 3840 x 2160p at 60Hz, which is perfect for performing high-resolution tasks such as viewing 4K video. Plus, the adapter is backward compatible with 1080p displays, which makes it a great travel accessory ensuring you can connect to any boardroom display or projector.

The CDP2HD4K60SA is backed by a 2-year StarTech.com warranty and free lifetime technical support.

**Note:** Your USB-C equipped device must support video to work with this adapter.

### Certifications, Reports and Compatibility



### Applications

- Be ready to present from your laptop, with the peace of mind in knowing your laptop will not enter power save mode when you don't want it to
- Keep this adapter with you while you travel to ensure you can connect to any HDMI display you come across
- Connect an HDMI display to your USB-C laptop to use as a secondary monitor

### Features

- Presentation Mode ensures your video output is not interrupted by your computer's power-saving modes
- Avoid the hassle of adjusting power settings, with an easy-to-use toggle switch that lets you turn Presentation Mode on or off
- Works on Mac and Windows computers
- Support for Ultra HD video resolutions up to 4K at 60Hz
- Hassle-free connection with the reversible USB-C connector
- Maximum portability with a small footprint and lightweight design
- Thunderbolt™ 3 port compatible
- 7.1 audio support

<b>Hardware</b>	Warranty	2 Years
	AV Input	USB Type-C
	AV Output	HDMI
	Ports	1
<b>Performance</b>	Audio Specifications	7.1 surround sound
	Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @ 60Hz
	Supported Resolutions	1024 x 768 1280 x 720 1920 x 1080 1920 x 1200 2560 x 1440 2560 x 1600 3840 x 2160
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - HDMI (19 pin) Female Output
<b>Special Notes / Requirements</b>	<b>Note</b>	This video adapter is not compatible with cables that use RedMere™ technology.
	System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
<b>Environmental</b>	Humidity	25% to 85% RH Non-Condensing
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	5°C to 35°C (41°F to 95°F)
<b>Physical Characteristics</b>	Accent Color	Black
	Cable Length	3.7 in [95 mm]
	Color	Black
	Product Height	0.6 in [16 mm]
	Product Length	7.5 in [190 mm]
	Product Weight	1 oz [28 g]
	Product Width	1.7 in [43 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	2.4 oz [67 g]
<b>What's in the Box</b>	Included in Package	1 - USB-C to HDMI video adapter 1 - quick-start guide

Product appearance and specifications are subject to change without notice.