

3 m (10 ft.) USB-C to VGA Cable - 1920 x 1200 - Black

Product ID: CDP2VGA3MBNL



This USB-C™ to VGA adapter cable offers a convenient solution for directly connecting your DisplayPort over USB Type-C™ device to your VGA monitor or projector. The adapter offers a connection distance of up to 3 m (10 ft.) and works with USB-C devices that support DP Alt Mode, such as the MacBook, Chromebook Pixel™ and Dell™ XPS™ models 15 and 13. It's also compatible with Thunderbolt™ 3 ports.

Clutter-free installation

At 3 m (10 ft.) in length, this adapter cable delivers a direct connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation.

For shorter installations, StarTech.com also offers a [1 m \(3 ft.\) USB-C to VGA cable \(CDP2VGAMM1MB\)](#) and [% product id="CDP2VGAMM2MB" text="2 m (6 ft.) USB-C to VGA cable (CDP2VGAMM2MB)"], enabling you to choose the right cable length for your custom installation needs.

Crystal-clear picture quality

The adapter harnesses the video capabilities that are built into your USB Type-C connector to deliver video resolutions up to 1920x1200, providing support for your high-resolution VGA monitors - great for multitasking on high-resolution VGA displays. The adapter is backward compatible with 1080p displays, which makes it a great accessory for home, office or other HD work environments.

The CDP2VGA3MBNL is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect a USB Type-C computer to a DVI projector or display in your classroom, auditorium or boardroom
- Install at your home workstation or office hot desk to make your USB-C computer compatible with your DVI display

Features

- Position your devices as needed throughout your workspace, with reduced cable clutter
- 3 m (10 ft.) all-in-one solution with a combined cable and adapter
- Hassle-free connection with the reversible USB-C connector
- Crystal-clear picture quality with support for video resolutions up to 1920x1200

Hardware	Warranty	2 Years
	AV Input	USB Type-C
	AV Output	VGA
	Chipset ID	Realtek - RTD2166 Realtek - RTS5404
	Ports	1
Performance	Maximum Analog Resolutions	1920x1200 or 1080p
	Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input 1 - VGA (15 pin, High Density D-Sub) Male Output
	Special Notes / Requirements	Note Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Environmental	Humidity	5%-90% RH (no condensation)
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	9.8 ft [3 m]
	Color	Black
	Product Height	0.6 in [14 mm]
	Product Length	118.1 in [3000 mm]
	Product Weight	4.6 oz [130 g]
	Product Width	0.9 in [22 mm]
Packaging Information	Shipping (Package) Weight	0.3 lb [0.1 kg]
What's in the Box	Included in Package	1 - USB-C to VGA cable

Product appearance and specifications are subject to change without notice.