

USB-C to VGA Adapter with USB Power Delivery - 60 Watts - Black

Product ID: CDP2VGAUCP



This USB-C to VGA adapter connects a VGA display to your laptop or MacBook with USB Type-C. The USB-C adapter features USB Power Delivery, enabling you to power your laptop while outputting video through the same USB-C port. The adapter is also available in [white](#) (CDP2VGAUCPW) so you can choose an adapter that matches the style of your laptop.

Power and Video in One Port with USB Power Delivery

Smaller and lighter laptops are great for portability but you're left with fewer connectivity ports. This USB-C VGA adapter supports USB Power Delivery up to 60 watts and features an additional USB-C port, so you can charge your laptop using its USB-C power adapter, even while you output video. Many laptops like Dell XPS and MacBook Pro support charging through your USB-C port with USB Power Delivery, check your specifications to confirm compatibility.

Enjoy HD Picture Quality with Video Resolutions up to 2048 x 1260

To ensure the quality of your video signal is maintained the USB-C dongle supports VGA resolutions up to 2048 x 1260 60Hz, including popular high-definition resolutions like 1080p and 720p.

Stylish Connectivity for Your Ultrabook or Any Laptop

This USB Type-C adapter has an all-black housing and built-in USB-C cable designed to match your Ultrabook or laptop. The adapter is compatible with any device that supports USB-C DP Alt Mode, such as the 2018 iPad Pro.

The CDP2VGAUCP is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect to any VGA display while travelling
- Connect your BYOD laptop to a VGA display at work, school or home while charging your laptop
- Present on a large VGA display using your USB-C laptop

Features

- Charge your laptop while connecting a VGA display using just one USB-C port, with USB Power Delivery
- Get crystal-clear picture quality with support for HD video resolutions up to 2048x1280 60Hz including 1080p
- Make the perfect connection, with a black USB-C adapter that exactly matches the cables for your Ultrabook or laptop

Hardware	Warranty	3 Years
	AV Input	USB Type-C
	AV Output	VGA
	Chipset ID	ITE - IT6516 VIA/VLI - VL100
Performance	Maximum Analog Resolutions	2048 x 1280 @ 60Hz
	Supported Resolutions	2048 x 1280 @ 60Hz 1920 x 1200 1920 x 1080 1280 x 720 1680 x 1050 1600 x 900 1440 x 900 1360 x 768 1280 x 800 1280 x 768
		<i>Lower resolutions and refresh rates may also be supported</i>
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female Output
		1 - USB-C (24 pin) USB Power Delivery only Female
Special Notes / Requirements	System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter
Power	Power Delivery	60W
	Power Source	USB-Powered
Physical Characteristics	Cable Length	4 in [102 mm]
	Color	Black
	Product Height	0.6 in [15 mm]
	Product Length	5.9 in [150 mm]
	Product Weight	0.8 oz [24 g]
	Product Width	1.3 in [33 mm]
Packaging Information	Shipping (Package) Weight	0.2 lb [0.1 kg]
What's in the Box	Included in Package	1 - USB-C to VGA adapter

Product appearance and specifications are subject to change without notice.