

2 Port CardBus eSATA Laptop Controller Adapter Card

Product ID: CBESAT2



This 2 port CardBus eSATA Adapter offers a cost-effective external storage solution that allows eSATA laptop connections to external SATA devices.

The eSATA laptop (PCMCIA) adapter is ideal for making routine backups or dumping data to SATA hard drives.

The eSATA CardBus Adapter presents a convenient way to protect your valuable data, with full external SATA data transfer speeds of up to 150MBps.

Certifications, Reports and Compatibility



Applications

- Enables effortless transport of high-capacity and high-performance Serial ATA hard drives
- Gives you 2 eSATA ports from your laptop
- With a quicker maximum data transfer rate (150MBps), it makes it easier to do data off loads

Features

- Compatible with 32-bit CardBus
- Data transfer rates up to 150MBps
- Plug and Play installation gets you up and running instantly
- Provides you with a faster transfer rate opposed to USB and FireWire
- Supports two high-speed eSATA channels for SATAI/II device connections
- Two external Serial ATA (eSATA) ports

Hardware	Warranty	Lifetime
	Bus Type	CardBus (PCMCIA)
	Chipset ID	Silicon Image - SiI3512
	Interface	eSATA
	Ports	2
Performance	Maximum Data Transfer Rate	150Mbps
	Port Multiplier	No
	RAID	No
	Type and Rate	SATA II (3 Gbps)
Connector(s)	Connector Type(s)	1 - PC Card (Type II, Cardbus) 2 - eSATA (7 pin, Data) Plug
Software	Microsoft WHQL Certified	Yes
	OS Compatibility	Windows 98SE/ ME/ 2000/ XP (32/64-bit)/ Server 2003 (32/64-bit)/ Server 2008 R2/ Vista (32/64-bit)/ 7 (32/64-bit) Linux 2.6 to 4.4.x <i>LTS Versions only</i>
Environmental	Humidity	0 to 85% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 85°C (14°F to 185°F)
Physical Characteristics	Product Height	0.6 in [15 mm]
	Product Length	4.5 in [115 mm]
	Product Weight	1.5 oz [42.9 g]
	Product Width	2.2 in [55 mm]
Packaging Information	Shipping (Package) Weight	0.8 lb [0.3 kg]
What's in the Box	Included in Package	1 - 2 Port eSATA CardBus Card 1 - Driver CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.