

2 Port CardBus Laptop USB 2.0 PC Card Adapter

Product ID: CBUSB22



This 2 Port CardBus USB 2.0 Adapter adds two USB 2.0 ports to your laptop or desktop computer, with support for full hi-speed USB data transfer rates of up to 480 Mbps.

The USB 2.0 CardBus adapter offers backward compatibility with USB 1.1 devices, ensuring seamless operation with older USB peripherals and supports hot-swappable operation to provide hassle-free peripheral connections without having to reboot the computer.

Designed to provide a permanent USB 2.0 solution, the CardBus adapter is backed by StarTech.com's Lifetime Warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect all kinds of external USB devices such as cameras, external hard drives, keyboards/mice to a laptop computer
- Add additional USB ports to a laptop to connect more devices
- Upgrade an old laptop with only USB 1.1 ports to be able to use USB 2.0 devices

Features

- High Speed USB 2.0 compliant host interface, with supported transfer rates up to 480 Mbps
- Backwards compatible with USB 1.1/1.0 devices
- Provides up to 500mA of power per port, with optional external power adapter
- Support for up to 127 USB devices per port (requires additional USB hubs)
- Plug and Play and Hot Swap compatible

Hardware	Warranty	Lifetime
	Bus Type	CardBus (PCMCIA)
	Chipset ID	VIA/VLI - VT6212
	Interface	CardBus
	Ports	2
Performance	Maximum Data Transfer Rate	480 Mbps
Connector(s)	Connector Type(s)	1 - PC Card (Type II, Cardbus) 2 - USB Type-A (4 pin) USB 2.0 Female
Software	Microsoft WHQL Certified	Yes
	OS Compatibility	Windows® 2000, XP, Vista, 7 Windows Server® 2003, 2008 R2 Mac OS X 10.10, 10.4.x, 10.3.x, 10.2.x Linux 3.5.x to 4.11.x <i>LTS versions only</i>
Special Notes / Requirements	System and Cable Requirements	Minimum Processor Requirements: Intel Pentium Pro, Pentium III, P4, or better
Power	Center Tip Polarity	Positive
	Output Current	1A+
	Output Voltage	5 DC
	Plug Type	H
	Power Source	Not Included (not required for standard applications)
Environmental	Operating Temperature	0°C to 85°C (32°F to 185°F)
	Storage Temperature	-55°C to 125°C (-67°F to 257°F)
Physical Characteristics	Product Height	0.6 in [1.5 cm]
	Product Length	4.5 in [11.5 cm]
	Product Weight	0.1 lb [0.1 kg]
	Product Width	2.2 in [5.5 cm]
Packaging Information	Shipping (Package) Weight	0.3 lb [0.1 kg]
What's in the Box	Included in Package	1 - CardBus USB 2.0 Card 1 - Driver CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.