

Under-Desk CPU Mount - Adjustable

Product ID: CPUMNTUD



Maximize your workspace. This under-desk CPU mount frees up floor and desk space, and gives you easy access to your computer tower.

Organize Your Office Space

The under-desk CPU holder provides an easy way to mount your computer under any desk or flat surface. It helps keep your work space neat and organized, by mounting your computer case off the desktop or floor, away from dust and dirt. The under-desk PC mount is ideal for mounting your CPU under a standing or sit-stand desk, moving the CPU up and down along with the desktop as needed.

Supports Most Computer Towers

The heavy-duty CPU holder has an adjustable frame that supports a variety of PC cases, ranging in width from 4.84" to 9.96" (123 mm to 253 mm) and height from 14" to 21.9" (357 mm to 557 mm).

Easy Access to Your Computer Tower

Offering a full 360-degree swivel, the under-desk PC mount provides easy access to your computer case, front and back, ensuring ports and cables are easy to reach. The under-desk CPU holder has a 10.09" (485 mm) long track with an easy-glide sliding mechanism that allows the CPU to move sideways for enhanced accessibility.

Protect Your Equipment

The heavy-duty computer tower mount securely holds your PC case, with a weight capacity of up to 66 lb. (30 kg).

CPUMNTUD is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount your computer under your desk or table to save space
- Ideal for mounting your CPU under a standing desk or sit-stand desk

Features

- Save space by mounting your PC case under your desk, off the floor
- Fits most CPU towers, with an adjustable frame (4.84" to 9.96" width and 14" to 21.9" height)
- Heavy-duty CPU mount securely holds up to 66 lb. (30 kg)
- Full 360-degree swivel for easy access to ports and cables
- Easy installation with all hardware needed for setup included

	Warranty	2 Years
Hardware	Mounting Options	Under Desk
Performance	Adjustable Frame	4.84" to 9.96" (123 mm to 253 mm) width and 14" to 21.9" (357 mm to 557 mm) height
	Swivel / Pivot	360°
	Weight Capacity (Per Display)	66.3 lb [30 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel and Plastic
	Product Height	26.2 in [66.5 cm]
	Product Length	8.4 in [21.3 cm]
	Product Width	10 in [25.3 cm]
	Weight of Product	11.1 lb [5 kg]
Packaging Information	Package Height	21.5 in [54.6 cm]
	Package Length	10.2 in [26 cm]
	Package Width	9.6 in [24.5 cm]
	Shipping (Package) Weight	12 lb [5.4 kg]
What's in the Box	Included in Package	1 - CPU Holder 1 - Mounting Plate 4 - Stoppers 2 - Stopper Screws 6 - Mounting Screws 1 - Foam Sheet 1 - User Manual

Product appearance and specifications are subject to change without notice.