

Aluminum Travel A/V Adapter: 4-in-1 USB-C to VGA, DVI, HDMI or mDP - 4K

Product ID: CDPVGDVHMDP



This 4-in-1 travel adapter offers a portable solution for connecting your USB-C computer to a VGA, DVI, HDMI® or Mini DisplayPort display.

The travel adapter is VESA certified to ensure compatibility with your DP alt mode computer. DP alt mode means your computer can pass a DisplayPort video signal through the USB-C port.



Stylish connectivity for your MacBook with USB-C

This travel adapter has been constructed with a sturdy aluminum housing and a built-in white USB-C cable. The adapter looks great and works well with any device that supports USB-C DP alt mode.



All-in-one video connectivity, with travel in mind

Instead of filling your laptop bag with different converters for different displays, this 4-in-1 adapter gives you all the video outputs you'll need. With VGA, DVI, HDMI and Mini DisplayPort outputs, this adapter lets you connect from your laptop's USB Type-C port to any boardroom or classroom display, without the inconvenience of carrying a separate adapter for each display type.

With support for multiple video outputs and a small-footprint design, this adapter is the ideal plug-and-play solution for travel or BYOD (Bring Your Own Device) applications around the office.



Innovative, built-in cable manager

The adapter features a built-in magnetic fastener, for cable management. The magnet helps guide the breakout cable into place for quick and secure storage while traveling, ensuring the adapter is neatly stored in your travel bag.

Astonishing picture quality

The HDMI and Mini DisplayPort outputs on this travel adapter support Ultra HD 4K resolutions providing four times the picture quality of high-definition 1080p. The HDMI and mDP outputs are also backward compatible with lower resolutions, such as 1080p and 720p, so the adapter is also perfect for your legacy video equipment. The VGA and DVI outputs also support a high-definition maximum resolutions of up to 1920 x 1200 so you can still enjoy excellent video quality.

The travel adapter is compatible with USB Type C Intel® Thunderbolt™ 3 devices that are capable of outputting a DisplayPort signal.

The CDPVGDVHDMDP is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Note: Your USB-C equipped device must support video to work with this adapter.

Certifications, Reports and Compatibility



Applications

- Keep the adapter with you while traveling, to connect to virtually any display
- Connect your BYOD MacBook to a provided VGA, DVI, HDMI or mDP display at work
- Connect a VGA, DVI, HDMI or Mini DisplayPort monitor to your MacBook, to use as a secondary monitor

Features

- 4-in-1 adapter - USB-C to VGA, USB-C to DVI, USB-C to HDMI and USB-C to Mini DisplayPort
- Maximum portability with built-in magnetic cable manager
- Astonishing picture quality with support for UHD 4K
- VESA certified
- Plug-and-play installation
- Small footprint
- Lightweight design
- Compatible with USB Type-C Thunderbolt™ 3 devices that are capable of outputting a DisplayPort signal

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	AV Input	USB Type-C
	AV Output	HDMI DVI-D VGA Mini-DisplayPort
	Chipset ID	Cypress - CYPD1120 Cypress - CY7C65210 Parade - PS8348B Parade - PS171
Performance	Audio Specifications	HDMI and mDP output - 7.1 surround sound
	General Specifications	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
	Maximum Analog Resolutions	1920 x 1200 @ 60Hz
	Maximum Digital Resolutions	3840 x 2160 @ 30Hz
	Supported Resolutions	Max HDMI output: 3840 x 2160 @ 30Hz Max mDP output: 3840 x 2160 @ 60Hz HDMI and mDP output: 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720 DVI and VGA output: 1920 x 1200, 1920 x 1080, 1280 x 720
	Video Revision	DisplayPort 1.2 HDMI 1.4
Wide Screen Supported	Yes	
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - Mini-DisplayPort (20 pin) Female Output 1 - VGA (15 pin, High Density D-Sub) Female Output 1 - DVI-D (25 pin) Female Output 1 - HDMI (19 pin) Female Output
Special Notes / Requirements	System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.

Environmental	Humidity	40%-50%RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Cable Length	4.3 in [110 mm]
	Color	Silver
	Product Height	0.6 in [15 mm]
	Product Length	4.1 in [105 mm]
	Product Weight	3.8 oz [108 g]
	Product Width	2.2 in [55 mm]
Packaging Information	Shipping (Package) Weight	6.5 oz [184 g]
What's in the Box	Included in Package	1 - travel A/V adapter

Product appearance and specifications are subject to change without notice.