

## 15 ft Long DisplayPort 1.2 Cable with Latches M/M – DisplayPort 4k

Product ID: DISPLPORT15L



The DISPLPORT15L DisplayPort™ 1.2 Cable with latches provides a secure connection between your DisplayPort-equipped devices and allows for a connection distance of up to 15-feet between your source and display.

The DP cable is capable of providing higher performance than either HDMI® or dual link DVI with support for high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz and a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The DISPLPORT15L long DisplayPort cable is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

### Certifications, Reports and Compatibility



### Applications

- Connecting a DisplayPort Display to a PC or other DisplayPort Source

### Features

- High-resolution support of up to 4k x 2k
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps
- Backward compatible with DisplayPort 1.1
- Designed and manufactured to DisplayPort 1.2 standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Molded latching connectors with strain relief

|                                 |                           |   |
|---------------------------------|---------------------------|---|
| <b>Hardware</b>                 | Warranty                  | Lifetime  |
|                                 | Cable Jacket Type         | PVC - Polyvinyl Chloride                        |
|                                 | Cable Shield Type         | Aluminum-Mylar Foil with Braid                  |
|                                 | Connector Plating         | Nickel  |
|                                 | Fire Rating               | CMG Rated (General Purpose)                     |
|                                 | Number of Conductors      | 19  |
| <b>Connector(s)</b>             | Connector A               | 1 - DisplayPort (20 pin) Latching Male          |
|                                 | Connector B               | 1 - DisplayPort (20 pin) Latching Male          |
| <b>Physical Characteristics</b> | Cable Length              | 15 ft [4.6 m]                                   |
|                                 | Cable OD                  | 0.3 in [7.3 mm]                                 |
|                                 | Color                     | Black   |
|                                 | Connector Style           | Latching  |
|                                 | Product Length            | 180 in [4572 mm]                                |
|                                 | Product Weight            | 11.7 oz [331 g]                                 |
|                                 | Wire Gauge                | 28 AWG  |
| <b>Packaging Information</b>    | Shipping (Package) Weight | 12 oz [340 g]                                   |
| <b>What's in the Box</b>        | Included in Package       | 1 - 15 ft DisplayPort® Cable with Latches - M/M |

Product appearance and specifications are subject to change without notice.