

# USB-C Multiport Adapter with HDMI and VGA - 1x USB-A

Product ID: DKT30CHVCM



Ideal for mobile workers, this USB-C multiport adapter with HDMI and VGA gives you flexible video output. It's like four adapters in one, with HDMI or VGA connections, a Gigabit Ethernet port and a USB 3.0 port, all through one connection to your laptop's USB-C port. Plus, it features a hideaway cable for better cable management and easier travel.

With easy plug-and-play installation on most operating systems, the USB-C adapter doesn't require additional drivers or software. It's the perfect accessory for MacBook Pro, Dell XPS, Chromebook or other USB-C laptops.

## Connect a UHD 4K HDMI or VGA Monitor

The USB Type-C multiport adapter keeps you prepared for business travel. You can extend your laptop's display by connecting to a 4K HDMI (4096x2160 or 3840 x 2160p) or VGA (1920 x 1200p) monitor or projector, to make presentations or set up a workstation.

## **Convenient Cable Management**

With multiple ports and an easily accessible hideaway cable, the USB-C all-in-one adapter makes an ideal travel dock, for easy connections on the go. Plus, the USB Type-C adapter is bus powered, so there's no need to carry around a separate power adapter.

## **Enhance Productivity**

Connect a flash drive, mouse or other peripheral to your USB-C or Thunderbolt 3 laptop using the USB 3.0 Type-A port. The USB-C adapter adds wired network connectivity with the GbE port, making it ideal in areas without Wi-Fi.

DKT30CHVCM is backed by a StarTech.com 3-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Make presentations in the boardroom or classroom, connecting to an HDMI or VGA monitor
- Ideal laptop accessory for mobile workers
- Convenient travel dock when working out of your hotel room
- Works well in small, shared and temporary workstations

### Features

- Connect your laptop to an external HDMI or VGA monitor with this USB-C multiport adapter
- Add a USB 3.0 Type-A device, like a flash drive or mouse
- Convenient hideaway cable attached, for enhanced cable management and portability
- Add wired network connectivity with the Gigabit Ethernet RJ45 port
- Bus-powered for easy portability

<b>Hardware</b>	Warranty	3 Years
	4K Support	Yes
	Bus Type	USB-C
	Chipset ID	Genesys Logic - GL3523 Realtek - RTL8153 Eton Technology - EJ899T Parade Technologies - PS176 ITE -IT6516
	Displays Supported	1
	Fast-Charge Port(s)	No
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1
<b>Performance</b>	Auto MDIX	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Maximum Analog Resolutions	1920 x 1200p @ 60Hz (VGA)
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
	Maximum Digital Resolutions	4096 x 2160p @ 24Hz or 3840 x 2160p @ 30Hz (HDMI)
	Type and Rate	USB 3.0 - 5 Gbit/s
	UASP Support	Yes
<b>Connector(s)</b>	Connector Type(s)	1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Male 1 - HDMI (19 pin) Female 1 - VGA (15 pin, High Density D-Sub) Female 1 - RJ-45 Female 1 - USB Type-A (9 pin) USB 3.0 Female
	OS Compatibility	Windows® 7, 8, 8.1, 10 macOS 10.11 to 10.14 Chrome OS™
	<b>Special Notes / Requirements</b>	<b>Note</b> Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your laptop USB-C port supports DP alt mode.  Only one video output port can be used at the same time (HDMI or VGA). If two displays are connected, the HDMI port takes priority.  A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K).

		USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.
	System and Cable Requirements	Host laptop with an available USB-C port (to ensure full functionality, the laptop's USB-C port must support DP alt mode).
<b>Power</b>	Power Source	USB-Powered
<b>Environmental</b>	Humidity	0~90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 70°C (-4°F to 158°F)
<b>Physical Characteristics</b>	Cable Length	3.3 in [85 mm]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.6 in [1.6 cm]
	Product Length	4.1 in [10.5 cm]
	Product Width	2.6 in [65 mm]
	Weight of Product	2.9 oz [82 g]
<b>Packaging Information</b>	Package Height	1.8 in [45 mm]
	Package Length	6.1 in [15.5 cm]
	Package Width	5.2 in [13.3 cm]
	Shipping (Package) Weight	0.4 lb [0.2 kg]
<b>What's in the Box</b>	Included in Package	1 - Multiport Adapter
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.