

3 ft DisplayPort to DVI Active Adapter Converter Cable - DP to DVI 1920x1200 - Black

Product ID: DP2DVIMM3BS



The DP2DVIMM3BS 3ft active DisplayPort to DVI converter cable lets you connect your DisplayPort-equipped desktop or laptop directly to a nearby DVI monitor or projector, saving the expense of additional adapters while eliminating the clutter of excess cable.

For guaranteed compatibility with virtually any DisplayPort output the active DisplayPort to DVI adapter supports multimode (DP++) as well as single-mode DisplayPort signals. Unlike passive adapters, this ensures the DP2DVIMM3BS can be used with graphics cards that are not capable of outputting multimode DP++ signals, such as ATI® Eyefinity cards.

Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to DVI without sacrificing video quality.

The DP2DVIMM3BS is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Note:

This adapter is not compatible for use with the Apple Cinema Display.

Certifications, Reports and Compatibility



Applications

- Use with single-mode DisplayPort video outputs that are not capable of outputting multimode DP++ signals, such as ATI® Eyefinity video cards
- Connect your DVI display device (monitor, projector) directly to a DisplayPort output device
- Ideal for using your DVI monitor as a secondary display

Features

- Active DisplayPort to DVI conversion
- 1x Male DisplayPort connector, 1x Male DVI connector
- Supports resolutions up to 1920x1200
- Plug-and-play Installation

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Adapter Style	Cable Adapters
	Audio	No
	AV Input	DisplayPort - 1.2
	AV Output	DVI-D - Single-Link
	Chipset ID	Parade - PS171
Performance	Audio Specifications	DVI - No Audio Support
	Maximum Cable Length	3 ft [0.9 m]
	Maximum Digital Resolutions	1920 x 1200
	Supported Resolutions	1024 x 768 1280 x 720 1920 x 1080 1920 x 1200
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - DisplayPort (20 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
Special Notes / Requirements	System and Cable Requirements	Some dual-link DVI monitors manufactured prior to 2014 may have limited resolutions support when used with this adapter. This adapter is not compatible for use with the Apple Cinema Display.
Environmental	Humidity	40%-85%RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	3 ft [0.9 m]
	Color	Black
	Product Height	0.6 in [1.5 cm]
	Product Length	36 in [91.5 cm]
	Product Width	1.6 in [40 mm]
	Weight of Product	2.6 oz [74.9 g]
Packaging Information	Package Height	0.6 in [15 mm]
	Package Length	8.7 in [22.2 cm]

	Package Width	7.8 in [19.7 cm]
	Shipping (Package) Weight	3.2 oz [91.6 g]
What's in the Box	Included in Package	1 - Active DisplayPort to DVI Adapter

Product appearance and specifications are subject to change without notice.