

DisplayPort to DVI Active Adapter

Product ID: DP2DVIS



The DP2DVIS DisplayPort to DVI Active Single Link adapter lets you connect your DisplayPort video source (desktop PC, laptop, etc.) to a DVI-D monitor, projector or display, including televisions and Apple Cinema Display HD, eliminating the expense of having to upgrade to a DisplayPort-capable monitor.

Unlike passive adapters, this DP to DVI converter offers an active conversion for use with any DisplayPort output - ideal for graphics cards that are not capable of outputting multi-mode DP++ signals (e.g. ATI Eyefinity). Supporting resolutions up to 1920x1200, this compact device provides a simple solution for converting DisplayPort output for compatibility with existing DVI monitors, televisions or projectors.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Keep your existing DVI monitor to be used with your new DisplayPort computer or source
- Great for using your DVI monitor as a secondary display
- Perfect for larger format screens that use high DVI resolutions
- Adapt from graphics cards that are not capable of outputting DP++ (multi-mode) signals

Features

- Supports resolutions up to 1920x1200
- Supported on any DVI-D display including televisions and Apple Cinema Display HD
- Latching DisplayPort connector
- Compliant with DisplayPort 1.1a specifications
- Supports HDCP 1.3
- Works with video cards not capable of outputting DP++ (multi-mode) signals

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	Audio	No
	AV Input	DisplayPort
	AV Output	DVI
	Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
	Industry Standards	HDCP 1.3 DisplayPort 1.1a DDWG 1.0
Performance	Maximum Digital Resolutions	1920x1200
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DVI-D (25 pin) Female
Environmental	Humidity	80~90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Color	Black
	Product Height	0.8 in [20 mm]
	Product Length	7.9 in [200 mm]
	Product Weight	1.7 oz [48 g]
	Product Width	1.7 in [44 mm]
Packaging Information	Shipping (Package) Weight	2 oz [57 g]
What's in the Box	Included in Package	1 - DisplayPort to DVI Adapter

Product appearance and specifications are subject to change without notice.