

USB-C Multiport Adapter with HDMI - 1x USB-A, 1x USB-C

Product ID: DKT30CHD



This USB-C Multiport Adapter with HDMI combines the capability of three single-function adapters, a USB-C video adapter, USB-C to USB 3.0 adapter, and Gigabit Ethernet adapter, into a portable docking station for your laptop. You can connect a 4K HDMI display and two USB 3.0 devices (1x USB-A, 1x USB-C), and get high-speed network access, all through a single cable.

The USB Type-C adapter is compatible with Thunderbolt 3 ports.

Add a 4K UHD Monitor

With HDMI output, this USB-C multiport adapter makes it easy to expand your virtual workspace onto an external 4K HDMI monitor. The adapter supports resolutions up to 4096 x 2160p (24Hz) or 3840 x 2160p (30Hz), as well as audio.

Reliable Network Access

The USB-C multiport adapter ensures a reliable wired network connection with a Gigabit Ethernet port, which is ideal for areas with limited Wi-Fi® access such as in classrooms, office buildings and hotels.

Connect Your USB Devices Easily

With two USB 3.0 ports (1x USB-A, 1x USB-C) you get access to traditional USB Type-A devices, as well as newer USB-C devices you add in the future.

Bring Productivity with You Wherever You Go

With its compact design and bus-powered performance, the portable multiport adapter is easy to take with you anywhere you take your laptop. The adapter features a pre-attached USB-C cable, so you have one less cable to carry when you're on the move.

The StarTech.com Advantage for Docking Stations

- **Maximum compatibility** - StarTech.com has a docking station to fit every operating system, laptop brand, and connectivity need
- **Get more done faster** - More ports and more displays maximize end user connectivity and productivity
- **Quick installation** - eliminate deployment headaches that waste time and frustrate end users
- **IT Grade quality** - trusted by IT pros around the world for our rigorous in-house product testing, robust compliance, and lifetime multilingual technical support

The DKT30CHD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Note: Your USB-C equipped host laptop must support video (DP Alt Mode) to work with this adapter. The adapter does not support USB Power Delivery.

Certifications, Reports and Compatibility



Applications

- Ideal for mobile use
- Integrate into small workspaces in offices and home offices

Features

- Add 4K HDMI, USB-A, USB-C and Gigabit Ethernet to your Thunderbolt 3 compatible Windows or MacBook laptop
- Easily connect an external 4K Ultra HD display (4096 x 2160p @ 24Hz or 3860 x 2160p @ 30Hz)
- Connect peripheral devices to the USB-A port (backward compatible with USB 2.0 and 1.x) and USB-C port
- Reliable, fast network connections with a Gigabit Ethernet port (RJ45), ideal for areas with limited Wi-Fi
- Bus-powered, supporting USB 3.0 (up to 5Gbps)

Hardware	Warranty	3 Years	
	4K Support	Yes	
	Bus Type	USB-C	
	Chipset ID	Genesys Logic - GL3523 Realtek - RTL8153 Parade - PS176	
	Displays Supported	1	
	Fast-Charge Port(s)	No	
Performance	Auto MDIX	Yes	
	Compatible Networks	10/100/1000 Mbps	
	Full Duplex Support	Yes	
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)	
	Maximum Digital Resolutions	4096 x 2160p @ 24Hz or 3840 x 2160p (HDMI) @ 30Hz	
	Type and Rate	USB 3.0 - 5 Gbit/s	
	UASP Support	Yes	
Connector(s)	Connector Type(s)	1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Female 1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Male 1 - HDMI (19 pin) Female 1 - RJ-45 Female 1 - USB Type-A (9 pin) USB 3.0 Female	
	Software	OS Compatibility	Windows® 7, 8, 8.1, 10 Mac OS 10.10 to 10.14 Chrome OS™
	Special Notes / Requirements	Note	Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your laptop USB-C port supports DP alt mode. A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K). USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps. The USB Type-C connector (female) is data only.
		System and Cable Requirements	Host laptop with an available USB-C port (to ensure full functionality, the laptop's USB-C port must support DP alt mode).
	Power	Power Source	USB-Powered

Environmental	Humidity	5~90% RH (Non-condensing)
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Cable Length	13.4 in [340 mm]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.6 in [15 mm]
	Product Length	2.6 in [65 mm]
	Product Weight	1.8 oz [52 g]
	Product Width	2.4 in [62 mm]
Packaging Information	Shipping (Package) Weight	0.4 lb [0.2 kg]
What's in the Box	Included in Package	1 - USB-C multiport adapter
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.