

## Black 3.5in IDE Hard Drive Mobile Rack for 5.25in Bay w/ fan

Product ID: DRW110ATABK



This high quality Removable ATA Hard Drive Drawer/Mobile Rack delivers a convenient storage solution, allowing you to quickly swap ATA66/ATA100 and ATA133 hard drives in and out of a computer without having to open the computer case.

Simply install the (included) drive bay into a 5.25in drive bay on the host computer, then mount a 3.5in ATA HDD in the (removable) caddy. Connecting the ATA hard drive to the computer is as easy as inserting the caddy into the drive bay, which can be locked to prevent unauthorized removal of the installed ATA drive.

A practical, time-saving storage solution, the drive drawer/mobile rack features front panel LED indicators that continuously display the operating status of the installed drive.

A suitable solution for large volume drives, the HDD drawer supports ATA66/ATA100 and ATA133 hard drives with a capacity of up to 750GB, allowing you to swap in large amounts of data in a matter of seconds.

The drive caddy features a rear panel ball-bearing fan that helps keep the enclosed drive cool, in turn helping to optimize operation while preserving drive lifespan. To prevent damage to the hard drive(s) while being transferred in and out of the computer, the drive caddy features shock absorbers and rubber cushioning that help limit vibration/shock to the drive.

A dependable, long-lasting storage solution, the drive drawer features highly durable construction, with a 3K insertion rating and is backed by StarTech.com's 2-year warranty.

### Certifications, Reports and Compatibility



### Applications

- Environments where drives need to be replaced/removed regularly, without external protection for the drives required after removal
- Be able to replace/remove individual drives from a storage array with minimal or no system down time
- Add additional hot-swap bays to a server or workstation computer
- System builders who need to image many drives simultaneously and quickly

### Features

- Fits a single IDE drive into a front accessible 5.25" bay
- Sturdy plastic construction for the drive caddy and bay
- Key lockable drive caddy
- Rubber shock absorbers
- 3,000+ insertion rating
- 40mm ball-bearing cooling fan
- Power LED indicator
- Fully supports ATA66/ATA100 & ATA133 drives and controllers
- Supports 3.5" form factor IDE hard drives

<b>Hardware</b>	Warranty	2 Years	
	Compatible Drive Types	IDE (ATA)	
	Drive Size	3.5in	
	Fan Bearing Type	Ball Bearing	
	Fans	1 - 40 mm	
	Front Door Key Lock	Yes	
	Interface	IDE	
	Number of Drives	1	
<b>Performance</b>	Hot Swap Capability	Yes	
	Shock Protection	Yes	
	Temperature Alarm	No	
<b>Connector(s)</b>	Connector Type(s)	1 - IDE (40 Pin, EIDE/PATA) Female 1 - IDE (40 Pin, EIDE/PATA) Male 1 - LP4 (4 pin, Molex Large Drive Power) Female 1 - LP4 (4 pin, Molex Large Drive Power) Male	
	<b>Special Notes / Requirements</b>	<b>Note</b> Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated  If you require the ability to insert/remove drives with the computer running, <a href="#">DRW113ATABK</a> includes Swap Manager for Windows	
	<b>Indicators</b>	LED Indicators	1 - Activity (Yellow) 1 - Power (Green)
		<b>Physical Characteristics</b>	Color
Enclosure Type	Plastic		
Product Height	1.6 in [41 mm]		
Product Length	8.7 in [220 mm]		
Product Weight	18.7 oz [530 g]		
Product Width	5.8 in [148 mm]		
<b>Packaging Information</b>	Shipping (Package) Weight	1.3 lb [0.6 kg]	
<b>What's in the Box</b>	Included in Package	1 - 3.5in Mobile Rack Caddy 1 - 5.25in Mobile Rack Bay	

2 - Keys

1 - Bag of mounting screws

1 - Instruction Manual

---

Product appearance and specifications are subject to change without notice.