

DVI to HDMI Video Adapter with USB Power and Audio - 1080p

Product ID: DVI2HD



This DVI to HDMI® adapter lets you connect your DVI laptop or desktop computer to an HDMI display or projector. The adapter works with any DVI output, but when you connect it to your Windows® computer, the adapter also supports native USB audio, allowing you to add your computer's audio to the HDMI output signal.

Hassle-free setup

The DVI to HDMI adapter is easy to use. The adapter features plug-and-play installation, so you won't need to load or download any special software, ensuring a fast and easy installation. The adapter also features a small footprint, ensuring it discreetly blends into your desktop setup, unlike bulky DVI adapter boxes that take up a lot of desk space.

If you want to transmit video only, you can just use the DVI connection. If you want to transmit audio as well as video, you can also plug in the USB connector. With no external power adapter needed, you have everything that you need in one compact solution.

Crystal-clear high-definition video

This adapter ensures that you're harnessing HD video quality from your DVI output, with support for resolutions up to 1080p.

The DVI2HD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Make your legacy DVI device compatible with a new HDMI television or projector
- Connect a DVI computer to an HDMI display at your desktop or workstation
- Convert DVI to HDMI and add audio to the HDMI signal

Features

- Adds 2-channel stereo audio to your HDMI output with USB audio
- Hassle-free setup with plug-and-play installation
- Crystal-clear picture quality with support for HD resolutions up to 1080p
- Compact and USB powered for maximum portability

Hardware	Warranty	3 Years	
	Adapter Style	Adapters	
	Audio	Yes	
	AV Input	DVI-D	
	AV Output	HDMI	
	Chipset ID	LT8522EX - CM108AH	
Performance	Audio Specifications	2-channel stereo audio	
	Maximum Digital Resolutions	1920 x 1080p at 60Hz	
	Supported Resolutions	1920x1080 (1080p) 1680x1050 (WSXGA+) 1600x1200 1600x900 1440x900 1400x1050 (SXGA+) 1366x768 1360x768 1280x1024 1280x960 1280x800 1280x768 (WXGA) 1280x720p (720p) 1280x600 1152x864 1024x768 800x600 (SVGA) 640x480 (480p)	
	Wide Screen Supported	Yes	
	Connector(s)	Connector A	1 - DVI-D (25 pin) Male Input
		Connector B	1 - HDMI (19 pin) Female Output
	Environmental	Humidity	40%-50%RH
		Operating Temperature	0°C to 70°C (32°F to 158°F)
		Storage Temperature	-10°C to 55°C (14°F to 131°F)
	Physical Characteristics	Color	Black
Enclosure Type		Plastic	
Product Height		0.6 in [14 mm]	
Product Length		10.1 in [257 mm]	
Product Weight		1.8 oz [50.1 g]	
Product Width		1.4 in [35 mm]	

Packaging Information	Shipping (Package) Weight	4.4 oz [126 g]
What's in the Box	Included in Package	1 - DVI to HDMI adapter 1 - quick install guide

Product appearance and specifications are subject to change without notice.