

Travel A/V adapter: 3-in-1 DisplayPort to VGA DVI or HDMI converter

Product ID: DP2VGDVHD



The DP2VGDVHD DisplayPort to VGA, DVI or HDMI converter offers a compact 3-in-1 solution for connecting your DP-equipped desktop, laptop or Ultrabook™ computer to a VGA, DVI, or HDMI display.

Compatible with almost any display, television or projector, this versatile converter provides the ideal plug-and-play solution for travel or BYOD (Bring Your Own Device) applications around the office. With three of the most common interfaces to choose from, the converter equips you to walk into any boardroom ready to connect to an available display device, even if you don't know what connection ports will be available.

For seamless connections from your DisplayPort-equipped computer, the converter supports video resolutions up to 1920x1200/1080p, so you can convert a DisplayPort video source to VGA, HDMI, or DVI without sacrificing video quality.

The DisplayPort converter offers a small footprint and lightweight design that makes it easy to keep on hand without it taking up too much space in your laptop bag.

The DP2VGDVHD is backed by a 3-year StarTech.com warranty and free lifetime technical support.



Certifications, Reports and Compatibility



Applications

- Keep the adapter with you while traveling, to connect to virtually any display
- Connect your BYOD laptop/Ultrabook to a provided HDMI, DVI, or VGA display at work
- Connect a DVI, VGA, or HDMI display to your DisplayPort computer, to use as a secondary monitor

Features

- Three-in-one adapter - DP to: VGA, DVI, HDMI
- Support for video resolution up to 1920x1200/1080p
- Plug-and-play installation
- Small footprint
- Portable, lightweight construction

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
		Passive
	Adapter Style	Adapters
	Audio	Yes
	AV Input	DisplayPort
	AV Output	DVI
HDMI		
VGA		
Performance	Audio Specifications	5.1 Surround Sound (Video source and destination dependant)
	Maximum Analog Resolutions	1920x1200/1080p
	Maximum Digital Resolutions	1920x1200/1080p
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DVI-D (25 pin) Female
		1 - HDMI (19 pin) Female
		1 - VGA (15 pin, High Density D-Sub) Female
Special Notes / Requirements	Note	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
		The HDMI port is a passive port. The DVI-D is a passive port. The VGA port is an active port.
Environmental	Humidity	10~85% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Cable Length	5.9 in [15 cm]
	Color	Black
	Product Height	0.6 in [15 mm]
	Product Length	11.2 in [284 mm]
	Product Weight	2.3 oz [65 g]
	Product Width	1.8 in [45 mm]

Packaging Information	Shipping (Package) Weight	2.6 oz [74 g]
What's in the Box	Included in Package	1 - DisplayPort to HDMI/VGA/DVI Adapter 1 - Installation Guide

Product appearance and specifications are subject to change without notice.