

DVI to Mini DisplayPort Adapter with Audio

Product ID: DVI2MDPA



The DVI2MDPA DVI to Mini DisplayPort® Adapter (with 2-Channel Audio) converts a DVI-D (Digital), Mini-DVI or HDMI source signal and accompanying audio, for use with a Mini DisplayPort or DisplayPort monitor at resolutions up to 1920x1200.

The adapter offers easy plug-and-play installation with both PC and Mac® platforms, ensuring seamless operation with your display to save the time and hassle of hardware upgrades.

A complete, out-of-the-box solution, this DVI-Mini DisplayPort adapter includes all cables necessary for connecting a DVI-D video source and 3.5mm stereo audio to any Mini DisplayPort monitor, including Apple Cinema HD® displays, and can also be used with Mini DVI or Mini HDMI sources using additional cables (sold separately - see Accessories).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Use a PC with a DVI or HDMI output with a Mini-DisplayPort monitor
- Convert DVI video and audio to one Mini DisplayPort input on monitors that support audio output
- Adapt a DVI-D output signal and connect supporting audio for use with Apple Cinema Displays

Features

- Supports resolutions up to 1920x1200
- USB power, 3.5mm audio and Mini-DisplayPort cables included
- Supports stereo audio pass-through to Mini-DisplayPort output (DisplayPort audio support required on monitor)
- Stores and passes EDID information
- USB-powered operation
- No software or drivers required

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Audio	Yes
	AV Input	3.5 mm Stereo Audio
		DVI-D
	AV Output	Mini-DisplayPort
	Industry Standards	Mini-DisplayPort 1.1a DVI 1.0
Performance	Maximum Digital Resolutions	1920x1200
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - 3.5 mm Mini-Jack (3 Position) Female Input 1 - DVI-D (25 pin) Male Input 1 - USB Mini-B (5 pin) Female
	Connector B	1 - Mini-DisplayPort (20 pin) Female Output
Special Notes / Requirements	Note	Can be used for HDMI input, or standard DisplayPort output using adapters - See Accessories
Indicators	LED Indicators	1 - Power indicator
Power	Input Voltage	5 DC
	Power Source	USB-Powered
Environmental	Humidity	10~85% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Cable Length	24 in [610 mm]
	Color	Black
	Enclosure Type	Aluminum and Plastic
	Product Height	0.6 in [14 mm]
	Product Length	3.3 in [83 mm]
	Product Weight	4.1 oz [116 g]
	Product Width	2.4 in [61 mm]
Packaging Information	Shipping (Package) Weight	0.5 lb [0.2 kg]
What's in the Box	Included in Package	1 - DVI to Mini-DisplayPort Converter

- 1 - 3.5mm Stereo Audio cable
- 1 - Mini DisplayPort cable
- 1 - USB mini B male to 2xA male (Split) Cable
- 1 - User Manual

Product appearance and specifications are subject to change without notice.