

DVI to VGA Video Converter with Scaler

Product ID: DVI2VGA



The DVI2VGA DVI to VGA Converter with Scaler allows you to convert a DVI Digital (DVI-D) signal to a VGA signal, saving you time and money by eliminating the need to purchase costly new hardware to make your devices compatible.

The scaler/converter features an easy to use On-Screen Display(OSD) that allows you to take full control of your display and the resolutions you need, in PC or HDTV mode. The OSD also features adjustments for brightness, color, contrast and horizontal/vertical positioning.

The DVI VGA Scaler/converter includes a plastic bracket for wall mounting, or side panel installation.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Allows you to connect your DVI video source (i.e. cable or satellite set top box, DVD player, computer) to a VGA or HDTV display
- A great way to make use of older display technology with a newer signal source

Features

- Converts DVI-D video input to Analog RGBHV or YPbPr output
- 48MB frame memory for frame rate conversion
- On-screen display allowing adjustments to brightness, contrast, color and Horizontal/Vertical positioning
- Includes a plastic bracket for wall mounts or side panel installation
- DVI source can be displayed onto a VGA or HDTV display using a VGA connector or component RCA connectors

| | | |
|-------------------------------------|----------------------------|--|
| Hardware | Warranty | 2 Years |
| | Audio | Yes |
| | AV Input | DVI |
| | AV Output | VGA |
| Performance | Maximum Analog Resolutions | PC Output - 1280x1024 max HD Output - 1080i/720p max |
| Connector(s) | Connector A | 1 - DVI-I (29 pin) Female Input |
| | Connector B | 1 - VGA (15 pin, High Density D-Sub) Female Output |
| Special Notes / Requirements | Note | Supports RGB, YPbPr, and YCbCr signals (VGA to Component cable not included - See Accessories) |
| Power | Center Tip Polarity | Positive |
| | Output Current | 2.6A |
| | Output Voltage | 5 DC |
| | Power Source | AC Adapter Included |
| Physical Characteristics | Color | Black |
| | Product Height | 1.2 in [30 mm] |
| | Product Length | 5.7 in [146 mm] |
| | Product Weight | 9.9 oz [280 g] |
| | Product Width | 3 in [77 mm] |
| Packaging Information | Shipping (Package) Weight | 2.4 lb [1.1 kg] |
| What's in the Box | Included in Package | 1 - DVI to VGA Converter/Scaler |
| | | 1 - 6ft (1.8m) DVI Cable |
| | | 1 - Power Adapter |
| | | 1 - User Manual |

Product appearance and specifications are subject to change without notice.