

USB 3.0 Multi Media Flash Memory Card Reader

Product ID: FCREADHCU3



The FCREADHCU3 USB 3.0 Card Reader enables easy read/write access to a variety of popular flash memory card formats/types (CompactFlash®, Secure Digital®, Memory Stick®) in a single unit, over a high speed USB 3.0 connection.

Using a connection over USB 3.0, which is up to 10 times faster than the USB 2.0 standard, makes transferring large data files much quicker; it (USB 3.0) is still backward compatible with USB 2.0 however, ensuring compatibility with older systems.

This compact and lightweight external card reader offers a portable, convenient solution for accessing many different types of Flash Memory/Media cards and is easy to use, with no driver or software installation required.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Laptop users looking to be able to access one or more types of flash memory cards
- Professionals looking to access their high speed flash memory cards over USB 3.0, instead of USB 2.0

Features

- Compatible with various types of CompactFlash®, SecureDigital® and MemoryStick® flash cards
- SuperSpeed USB 3.0 host interface standard, which supports transfer rates up to 5 Gbps
- Powered directly from the USB port
- Backward compatible with USB 2.0 computer systems
- Power indicator LED
- Compact design and lightweight plastic construction
- No driver or software installation required

Hardware	Warranty	2 Years
	Chipset ID	Genesys Logic - GL3220
	Interface	USB 3.0
Performance	Memory Media Type	CF (Compact Flash I Card)
		M2 (Memory Stick Micro)
		microSDHC (Micro Secure Digital High Capacity)
		Mini-SD, Micro-SD (Mini/Micro Secure Digital)
		MS Duo, MS Pro Duo, MS Pro-HG Duo
		MS MG (Memory Stick w/ MagicGate)
		MS/MS Pro (Memory Stick/Memory Stick Pro)
		MSXC (Memory Stick eXtended Capacity)
		RS-MMC (Reduced Size Multimedia Card)
		SD/MMC (Secure Digital/Multimedia Card)
Connector(s)	Connector Type(s) External Ports	1 - USB Type-B (9 pin) USB 3.0 Female
		1 - CompactFlash (50 pin) Slot
		1 - Memory Stick / Memory Stick Pro Slot Female
		1 - MiniSD / MicroSD / MMC Slot Female
		1 - SD / MMC Slot Female
Software	OS Compatibility	OS independent; No software or drivers required
Special Notes / Requirements	System and Cable Requirements	Available USB port
Indicators	LED Indicators	1 - Power
Power	Input Current	0.8 A
	Input Voltage	100 ~ 240 AC
	Output Current	4 A
	Output Voltage	5 DC
	Power Consumption (In Watts)	20
	Power Source	USB-Powered
Environmental	Humidity	5% ~ 90% RH
	Operating Temperature	-40°C to 80°C (-40°F to 176°F)

	Storage Temperature	-65°C to 150°C (-85°F to 302°F)
Physical Characteristics	Color	Black
	Enclosure Type	Plastic
	Product Height	0.8 in [20 mm]
	Product Length	3.3 in [85 mm]
	Product Weight	1.9 oz [54 g]
	Product Width	2.2 in [55 mm]
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	6 oz [169 g]
What's in the Box	Included in Package	1 - USB 3.0 Card Reader
		1 - USB 3.0 Cable
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.