

USB 3.0 Flash Memory Multi-Card Reader / Writer with USB-C - SD, microSD, CompactFlash

Product ID: FCREADU3C



Ideal for creative professionals, this multi-card reader/writer saves you time and helps you work more efficiently when working with a wide variety of flash media, letting you quickly transfer and back-up files. It supports SD™ (Secure Digital), microSD™, and CompactFlash® cards, and connects to the USB-C™ port on your tablet, smartphone, laptop or desktop computer.

Fast data transfers to increase workflow efficiency

The multi-card reader makes it easy to offload photos, video, and other files you've saved on your memory cards, providing fast access through USB 3.0 (also known as USB 3.1 Gen 1) with file transfer speeds up to 5Gbps. The reader increases workflow efficiency for creative professionals such as photographers and videographers. It helps to increase your productivity by saving you time when offloading raw images or editing video and photos, and backing up files.

The card reader is also backward compatible with USB 2.0, ensuring compatibility with older systems.

Supports a wide variety of flash media for flexible use

This multi-card flash reader gives you the flexibility and convenience of accessing multiple types of memory cards. It gives you read and write access to virtually any format of flash media card from your digital cameras or video cameras, with support for SD, SDHC™ (Secure Digital High Capacity), SDXC™ (Secure Digital Extended Capacity), microSD and CompactFlash cards. You can easily review files or back up and archive data from your smartphone, tablet, laptop or other USB Type-C enabled device. The three memory card slots for SD, microSD, and CompactFlash cards are all hot swappable, for additional flexibility.

Convenient portability

The card reader gives you a portable solution for accessing a wide variety of memory cards anywhere you go. With its small form factor, it fits easily into your pocket, backpack, briefcase or laptop bag. The integrated USB Type-C cable lets you quickly connect to a computer or pack it up quickly when you're done using it, without having to carry an additional cable with you. The card reader is powered directly from the USB port and supports plug-and-play installation, with no driver or software installation required.

The FCREADU3C is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Transfer photos, videos or other files from your SD, microSD, and CompactFlash cards to your USB-C enabled tablet, laptop or other device
- Gain greater efficiency when working with a variety of memory cards - ideal for creative professionals including photographers, videographers, and graphic designers

Features

- Transfer photos, videos, music and other files to and from your memory card to your USB-C enabled tablet, laptop, smartphone or desktop computer
- Multi-card flash reader and writer supports Secure Digital, microSD and CompactFlash cards
- Supports USB 3.0 with data transfer speeds up to 5Gbps (USB powered)
- Thunderbolt 3 USB-C port compatible
- Compact, portable design with stylish brushed-aluminum housing
- Backward compatible with USB 2.0
- No driver or software installation required

Hardware	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	Realtek - RTS5309
	Interface	USB 3.0
Performance	Maximum Data Transfer Rate	5 Gbps
	Memory Media Type	SD/MMC (Secure Digital/Multimedia Card)
		SDHC (Secure Digital High Capacity)
		SDXC (Secure Digital eXtended Capacity)
microSD (Micro Secure Digital)		
	microSDHC (Micro Secure Digital High Capacity)	
	microSDXC (Micro Secure Digital eXtended Capacity)	
	CF (Compact Flash I Card)	
	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	Drive Connectors	1 - microSD
		1 - SD / MMC
		1 - CompactFlash (50 pin) Slot
	Host Connectors	1 - USB Type-C (24 pin) USB 3.0 Receptacle
Software	OS Compatibility	OS independent; No software or drivers required
Special Notes / Requirements	System and Cable Requirements	Available USB port
Environmental	Humidity	5% ~ 90% RH
	Operating Temperature	-20°C to 70°C (-4°F to 158°F)
	Storage Temperature	-20°C to 75°C (-4°F to 167°F)
Physical Characteristics	Color	Silver & Black
	Enclosure Type	Aluminum and Plastic
	Product Height	0.6 in [14 mm]
	Product Length	2.7 in [68 mm]
	Product Weight	2.4 oz [67 g]
	Product Width	2.5 in [64 mm]
Packaging Information	Shipping (Package) Weight	3.7 oz [104 g]
What's in the Box	Included in Package	1 - multi-card reader and writer

1 - quick-start guide

Product appearance and specifications are subject to change without notice.