

## 20-Slot 2U Rack Mount Media Converter Chassis for ET Series 2 Fiber Media Converter

Product ID: ETCHS2U



The ETCHS2U 20-Slot 2U Rack Mount Media Converter Chassis for ET Series 2 Media Converters lets you add an un-managed, 20-slot media converter chassis to your rack or cabinet to provide central power and cooling.

The media converter rack includes a single 200W power supply to centrally power all 20 slots, with an additional slot to add a [redundant power supply](#) (ETCHS2UPSU) for maximum up-time. It also includes two cooling fans (one per side) to help extend the life of your media converters.

A perfect accessory to the StarTech.com ET series 2 converters, the 2U chassis is designed so that all critical components (Power, Fans and Media Converter Cards) are hot swappable to avoid network disruption.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Centrally mount and power up to 20 media converter units with a single chassis, while providing additional cooling and optional redundant power

### Features

- 2U 20-slot Media Converter Chassis with AC/DC power
- Single 200W Power Supply included - [redundant power supply](#) (ETCHS2UPSU) also available - sold separately
- 2 removable cooling fans included
- All modules and cards support hot-swapping

<b>Hardware</b>	Warranty	2 Years
	Fan(s)	Yes
	Fans	2 - 80 mm
	Frame Type	Open Frame
	Mounting Options	Front Mount (Front Only)
	U Height	2U
<b>Performance</b>	Air Flow Rate	59.37 CFM
	MTBF	65,000 Hours (25°C)
	Noise Level	44.5 dBA
<b>Power</b>	Input Current	2.2 A
	Input Voltage	110V-240V AC
	Output Current	16.6 A
	Output Voltage	12 DC
	Power Consumption (In Watts)	60
	Power Source	Standard 120V Power Cords
<b>Environmental</b>	Humidity	5~90% RH Non-condensing
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Product Height	6.5 in [164 mm]
	Product Length	15.5 in [394 mm]
	Product Weight	13.4 lb [6.1 kg]
	Product Width	20.4 in [517 mm]
	Rail Thickness	0 in [1 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	18.5 lb [8.4 kg]
<b>What's in the Box</b>	Included in Package	1 - 2U Media Converter Chassis
		3 - Power Cords (NA/EU/UK)
		1 - Grounding Screw
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.