

## Full-Motion TV Wall Mount - Articulating Arm

Product ID: FPWARTB1M



Maximize space while creating an impressive display. This full-motion TV wall mount, made of heavy-duty steel, securely supports flat-screen TVs from 32" to 55". The arm extends easily to provide smooth, full-motion positioning for ideal viewing.

### Mount Your Monitor to Save Valuable Space

Mount your flat-screen TV in a location that's convenient for visitors, clients and employees. This TV wall mount is ideal for the lobby, boardroom or other venues, providing an impressive and secure way to display a flat-panel TV or mount digital signage. It also frees up valuable space. The TV wall mount supports most 32" to 55" (558.8 to 1397 mm) LED or LCD flat panel TVs weighing up to 77 lb. (35 kg).

### Full-Motion Adjustment

The TV wall mount provides full-motion adjustment capability. The arm extends up to 19.8" (503 mm) from the wall to provide a wide range of movement and accommodate different screen positions and angles. The arm can also fold to tuck-in closely to the wall, providing a minimized profile, which enables you to position your display just 1.9" (49 mm) from the wall.

The TV wall mount swivels +90 / -90 degrees to provide maximum viewing flexibility. The mount also tilts +2 / -12 degrees, letting you angle your TV display toward your audience. With the tilt feature, you can mount your TV lower or higher than eye level and still view it comfortably.

### **Heavy-Duty Construction**

The robust steel design safely and securely supports your flat-screen TV, to protect your investment. The TV wall mount also includes plastic brackets for cable management to keep cables neatly out of sight.

The FPWARTB1M is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Securely wall-mount your TV for easy viewing in boardrooms, lobbies, classrooms and meeting spaces
- Keep guests informed in hotels, restaurants and other venues
- Save space by wall-mounting your TV in your home theater

### Features

- Save space with this flat-screen TV wall mount for 32" to 55" TVs (fits curved TVs, with compatible VESA mount)
- Full-motion adjustment with arm extension up to 19.8" (503 mm)
- The arm can tuck in closely to the wall, extending only 1.9" (49 mm)
- Tilts +2 /-12 degrees for easy angle adjustment, and arm swivels +90 /-90 degrees for viewing flexibility
- Heavy-duty steel TV wall mount supports up to 77 lb. (35 kg)

<b>Hardware</b>	Warranty	5 Years
	# of Displays Supported	1
	Articulating	Yes
	Cable Management	Yes
	Minimum Profile from Wall	1.9 in [49 mm]
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	100x100 mm
		100x150 mm
		200x100 mm
		200x200 mm
		300x200 mm
		300x300 mm
		400x200 mm
400x300 mm		
400x400 mm		
Wallmountable	Yes	
<b>Performance</b>	Anti-theft	No
	Display Tilt	+2° / -12°
	Fits Curved Display	Yes
	Maximum Arm Extension	19.8 in [503 mm]
	Maximum Display Size	55"
	Minimum Display Size	32"
	Swivel / Pivot	+90° / -90°
	Video Wall	No
Weight Capacity (Per Display)	77.4 lb [35 kg]	
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel and Plastic
	Product Height	15.7 in [40 cm]
	Product Length	15.7 in [40 cm]
	Product Width	24.2 in [61.4 cm]
	Weight of Product	6.2 lb [2.8 kg]

<b>Packaging Information</b>	Package Height	2 in [50 mm]
	Package Length	12.7 in [32.3 cm]
	Package Width	15.6 in [39.5 cm]
	Shipping (Package) Weight	7.7 lb [3.5 kg]
<b>What's in the Box</b>	Included in Package	1 - wall mount
		4 - VESA extension brackets
		4 - bracket screws
		4 - nuts
		1 - wrench
		4 - M5x14 mm screws
		4 - M6x14 mm screws
		4 - M6x30 mm screws
		4 - M8x30 mm screws
		4 - M8x50 mm screws
		4 - small washers
		4 - large washers
		8 - small spacers
		8 - large spacers
4 - screws		
4 - concrete screws		
4 - bracket washers		
1 - instruction manual		

Product appearance and specifications are subject to change without notice.