

# USB 3.0 External Flash Multi Media Memory Card Reader - SDHC MicroSD

Product ID: FCREADMICRO3



The FCREADMICRO3 USB 3.0 Multi-media Card Reader offers quick access to the most popular flash card formats, from any computer with a USB port (optimal performance with 3.0, backward compatible with USB 2.0).

Suitable for quickly accessing memory cards of virtually any portable media device (e.g. digital cameras, MP3 players, etc.), this versatile media card reader supports the most popular card types, including:

- Secure Digital (SD)
- Multi-Media Card (MMC)
- Mini-SD, Micro-SD/SDHC (T-flash)
- SDHC
- SDXC
- RS-MMC
- Mobile-MMC and MMC-micro
- Memory Stick (MS)
- Memory Stick PRO (MS-PRO)
- MS Duo

- MS-PRO Duo
- Memory Stick XC
- Micro-MS (M2)
- MSPRO-HG Duo 8-bit mode.

An ideal Laptop or Desktop accessory, this pocket-sized memory card reader is lightweight, portable, and backed by a StarTech.com 2-year warranty with free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Mobile users/travelers who need a compact and lightweight card reader small enough to fit in a pocket
- Photographers who need to regularly transfer files from their camera memory card to a computer
- Transferring files to and from a variety of portable devices, each using a different memory card format

### Features

- High Speed USB 3.0 host interface with support for transfer rates up to 5 Gbps
- Support for Secure Digital (SD), MultiMedia Card (MMC), Mini-SD, Micro-SD/SDHC (T-flash), SDHC, SDXC, RS-MMC, Mobile-MMC and MMC-micro, Memory Stick (MS), Memory Stick PRO (MS-PRO), MS Duo, MS-PRO Duo, Memory Stick XC, Micro-MS (M2), and MSPRO-HG Duo 8-bit mode
- Ultra-compact and lightweight design
- Powered directly from the USB port
- Plug-and-Play and Hot-Swap compatible

<b>Hardware</b>	Warranty	2 Years		
	Bus Type	USB 3.0		
	Chipset ID	Realtek - RTS5307		
	Interface	USB 3.0		
<b>Performance</b>	Maximum Data Transfer Rate	5 Gbit/s		
	Memory Media Type	HS-MMC, HC-MMC (High Speed/High Capacity Multimedia Card) M2 (Memory Stick Micro) Memory Stick microSDHC (Micro Secure Digital High Capacity) MS Duo, MS Pro Duo, MS Pro-HG Duo MS Micro (Memory Stick Micro) MSXC (Memory Stick eXtended Capacity) Multi Media Card RS-MMC (Reduced Size Multimedia Card) SD/MMC (Secure Digital/Multimedia Card) SDHC (Secure Digital High Capacity) SDXC (Secure Digital eXtended Capacity)		
	<b>Connector(s)</b>	Connector Type(s)	1 - USB Type-A (9 pin) USB 3.0 Male	
		External Ports	1 - Memory Stick / Memory Stick Pro Slot Female 1 - MicroSD Female 1 - SD / MMC Slot Female	
		<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
		<b>Power</b>	Power Source	USB-Powered
	<b>Environmental</b>	Humidity	< 80% R.H.	
		Operating Temperature	0°C to 40°C (32°F to 104°F)	
		Storage Temperature	-20°C to 60°C (-4°F to 140°F)	
	<b>Physical Characteristics</b>	Color	Black	
Enclosure Type		Plastic		
Product Height		0.6 in [15 mm]		
Product Length		2.8 in [72 mm]		

	Product Weight	0.5 oz [15 g]
	Product Width	0.9 in [23 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	3.7 oz [104 g]
<b>What's in the Box</b>	Included in Package	1 - USB 3.0 Multi Media Memory Card Reader Adapter 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.