

## Flat-Screen TV Wall Mount - Low Profile - For 37" to 75" TV - Anti-Theft - Fixed

Product ID: FPWFXBAT



Save space while improving the appearance of your work area, with this low-profile TV wall mount. The mount sits close to the wall to support a VESA Mount compliant TV from 37" to 75", and offers anti-theft protection.

### Low-profile design for meeting areas or digital signage

Mount your flat-screen TV or monitor in a location that's convenient for visitors, clients or employees. The wall mount safely and securely supports your TV in a fixed position, less than an inch (22 mm) from the wall, to provide a sleek, low-profile look.

It's ideal for lobbies, hallways, boardrooms, works areas, customer-facing areas or for creating digital signage. The wall mount supports most 37" to 75" (940 to 1905 mm) LED or LCD flat panel TVs weighing up to 88 lb. (40 kg).

## **Anti-theft protection**

Engineered with heavy-duty steel, the robust steel TV wall mount securely supports your flat-screen TV, to protect your investment. Ideal for areas with high traffic and minimal supervision, the TV mount features a steel bar that can be locked into place with a padlock (purchased separately) to protect your TV or monitor against theft.

## **Easy setup**

A built-in level helps to ensure your TV is aligned in a straight position on your wall, to ensure optimum viewing.

The FPWFXBAT is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Securely wall-mount your flat-screen TV in a classroom, lecture hall, or meeting space, or in a customer-facing area such as a lobby
- Keep your guests informed or entertained, ideal in hotels, restaurants and other hospitality venues
- Protect your TV or monitor against theft with the lockable bar, ideal for areas with high traffic and minimal supervision

### Features

- Save space by wall-mounting your 37" to 75" TV
- Low-profile TV mount sits less than 1" (only 22 mm) from the wall
- Lockable bar securely holds TV and provides anti-theft protection (padlock required), ideal for high traffic or unsupervised areas
- Heavy-duty steel TV wall mount supports up to 40 kg (88 lb.)
- Built-in level ensures ideal positioning during installation
- Supports VESA Mount compliant TVs: 200x200, 300x300, 400x200, 400x400, 600x400, 800x400

<b>Hardware</b>	Warranty	5 Years
	# of Displays Supported	1
	Articulating	No
	Cable Management	No
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	200x200 mm
		300x300 mm
		400x200 mm
400x400 mm		
600x400 mm		
800x400 mm		
<b>Performance</b>	Anti-theft	Yes
	Maximum Display Size	75"
	Minimum Display Size	37"
	Video Wall	No
	Weight Capacity (Per Display)	88.4 lb [40 kg]
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel and Plastic
	Product Height	17.3 in [440 mm]
	Product Length	35.4 in [898 mm]
	Product Weight	6.4 lb [2.9 kg]
	Product Width	1.1 in [29 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	9 lb [4.1 kg]
<b>What's in the Box</b>	Included in Package	1 - wall mount
		1 - safety bar
		2 - adapter brackets
		1 - level
		2 - decorative covers
		4 - decorative cover screws
		4 - M5x14 mm screws

- 4 - M6x14 mm screws
- 4 - M8x50 mm screws
- 4 - M6x30 mm screws
- 4 - M8x30 mm screws
- 4 - rectangular washers
- 8 - small spacers
- 8 - large spacers
- 6 - screws
- 6 - concrete anchors
- 6 - circular washers
- 1 - instruction manual

---

Product appearance and specifications are subject to change without notice.