

4-Port USB 3.0 Hub - 4x USB-A with Individual On/Off Switches

Product ID: HB30A4AIB



This portable USB 3.0 hub gives you an easy way to add four USB 3.0 Type-A ports to your laptop, with individual power switches to save power. The USB port expander plugs easily into your laptop's USB Type-A port. Plus, it's bus-powered for easy portability.

Connect Your Current USB Devices

Use your existing USB 3.0 devices such as flash drives, mouse, keyboard and external hard drives. The 4-port USB 3.0 hub expands your computer's USB Type-A port into four USB 3.0 (Type-A) ports, and it's backward compatible with your older USB 2.0 devices. (USB 3.0 is also known as USB 3.1 Gen 1.)

Individual On/Off Switches

Each port on the USB 3.0 hub has its own power switch so you can turn off devices when they're not in use. That means you can better manage power consumption for your USB devices, without having to physically disconnect the device or cable.

Easy Portability

With its compact, lightweight design, this hub is perfect for portable use. The versatile USB to USB hub is bus-powered, with no need for an external power adapter. You can travel lighter with fewer cables to carry with you.

Plug and Play

The 4-Port USB 3.0 hub installs automatically when you connect it to your laptop, so you can be up and running in seconds.

HB30A4AIB is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Take the hub with you when you travel, to connect your USB devices
- Switch unused ports off when using high power-consuming USB equipment
- Perfect for office, hot-desk, home office and bring-your-own-device environments

Features

- Add four USB 3.0 (Type-A) ports to your Mac, Windows®, Linux® or other laptop with this USB 3.0 hub
- Save power with On/Off power switches for each USB port
- USB bus-powered, with no external powered required
- Compact, portable design with attached cable (9.8 in./25 cm)
- Save time with plug-and-play installation

Hardware	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	VIA/VLI - VL817
	Fast-Charge Port(s)	No
	Industry Standards	USB 3.1 Gen 1 (USB 3.0) - Backward compatible with USB 2.0 and 1.1
	Interface	USB 3.0
	Ports	4
	USB-C Device Port(s)	No
	USB-C Host Connection	No
Performance	Maximum Data Transfer Rate	5 Gbps
	Type and Rate	USB 3.0 - 5 Gbit/s
	UASP Support	Yes
Connector(s)	Connector Type(s)	4 - USB Type-A (9 pin) USB 3.0 Female 1 - USB Type-A (9 pin) USB 3.0 Male
Software	OS Compatibility	OS Independent; No additional drivers or software required
Special Notes / Requirements	System and Cable Requirements	Available USB Type-A port - USB 3.0 (5Gbps)
		The total available power output of the HB30A4AIB is based on the available input power and is shared between all downstream facing ports.
Indicators	LED Indicators	4 - Port Power
Power	Power Source	USB-Powered
Environmental	Humidity	20~80% RH (Non-condensing)
	Operating Temperature	0°C to 55°C (32°F to 131°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	9.8 in [250 mm]
	Enclosure Type	Plastic
	Form Factor	Compact
	Product Height	0.8 in [19.2 mm]
	Product Length	3.3 in [85 mm]
	Product Weight	1.5 oz [43 g]

	Product Width	1.4 in [34.9 mm]
Packaging Information	Shipping (Package) Weight	3.8 oz [107 g]
What's in the Box	Included in Package	1 - hub 1 - quick-start guide

Product appearance and specifications are subject to change without notice.