

Compact HDMI to VGA Adapter Converter - Ideal for Chromebooks Ultrabooks & Laptops – 1920x1200/1080p

Product ID: HD2VGAMICRO



The HD2VGAMICRO HDMI to VGA converter lets you connect an HDMI output from your, Chromebook, Ultrabook or laptop computer to a VGA monitor or projector.

To ensure compatibility with your Samsung® Chromebook the HD2VGAMICRO has been extensively tested in wide range of applications, making the video adapter an ideal converter to connect your Chromebook to any VGA display.

With no external power adapter required, and a small form factor design, this portable HDMI to VGA adapter is a great accessory to have on-hand in your laptop carrying case. Plus, this easy-to-use converter supports plug-and-play installation, which speeds up the installation time and eliminates the worry of having driver software ready on any computer.

The converter delivers maximum video quality, with support for resolutions up to 1920x1200/1080p -- a convenient solution for boosting productivity by extending your computer's desktop onto a secondary monitor.

The HD2VGAMICRO is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- In an office boardroom connect HDMI-enabled devices such as your laptop, or Ultrabook computer to a VGA projector or large screen display
- Increase your productivity by extending your computer's desktop onto a secondary monitor, doubling available workspace
- Connect an HDMI-equipped Chromebook, Ultrabook or laptop to an external VGA display or projector

Features

- No power adapter required
- Small form factor
- Support for resolutions up to 1920x1200/1080p

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Audio	No
	AV Input	HDMI
	AV Output	VGA
	Ports	1
Performance	Maximum Analog Resolutions	1920x1200
	Supported Resolutions	1920x1200, 1920x1080 (1080p), 1600x1200 @ 60Hz
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - HDMI (19 pin) Male Input
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female Output
Environmental	Humidity	20~90% RH Non-Condensing
	Operating Temperature	-20°C to 85°C (-4°F to 185°F)
	Storage Temperature	-20°C to 85°C (-4°F to 185°F)
Physical Characteristics	Color	Black
	Product Height	0.6 in [14 mm]
	Product Length	1.8 in [45 mm]
	Product Weight	0 oz [0 g]
	Product Width	0.8 in [21 mm]
Packaging Information	Shipping (Package) Weight	0.4 oz [11 g]
What's in the Box	Included in Package	1 - Slim HDMI to VGA Adapter Converter

Product appearance and specifications are subject to change without notice.