

3-Port USB-C Hub with Gigabit Ethernet - USB-C to 3x USB-A - USB 3.0 Hub - White

Product ID: HB30C3A1GEA



Here's a must-have accessory for your USB-C™ equipped MacBook Pro, Chromebook™ or laptop. This USB 3.0 hub merges your USB peripheral and RJ45 network connections into a single combination hub. It gives you two vital connection types, with Ethernet and USB Type-A, which are often missing from modern laptops.

Easily connect to your network and peripherals through USB-C

This 3-port USB hub features an easy-to-use USB-C connector. USB Type-C connectors are easier to insert than past generations. They're small and reversible, and you can connect the plug with either side facing up.

Merges two vital port types into one stylish hub

If your MacBook or laptop is missing the ports you need, this hub can help. USB 3.0 is also known as USB 3.1 Gen 1. The versatile USB 3.0 hub gives you access to not only your USB peripheral devices but also a wired internet connection. It offers a Gigabit Ethernet port, so you can connect to a network in locations where Wi-Fi® is unreliable or unavailable.

The stylish USB hub features an attractive white finish.

Rugged, portable, and bus powered

The hub features a rugged yet lightweight housing, so there's no need to sacrifice dependability for portability. Its USB-powered design means you don't need to carry a separate power adapter, so you can tuck the USB 3.0 hub neatly into your travel bag.

This hub is perfect for travel, and it takes up minimal space on a desk, so you can use it in hot-desk or BYOD (Bring Your Own Device) environments.

Built-in cable eliminates aggravation

The hub's built-in USB-C cable makes connections easy, and you don't need to carry a separate cable to attach the hub to your laptop.

The HB30C3A1GEA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Take advantage of USB-C by using the hub to connect to both a network and USB peripherals to your USB-C equipped laptop
- Upgrade the connection capabilities of your MacBook Pro
- Carry the hub with you while you're traveling, and connect your USB devices wherever you go
- Ideal for desktop, laptop, Ultrabook™, Chromebook, and MacBook users who don't have enough USB 3.0 ports available
- Add wired internet connectivity to your laptop in settings where Wi-Fi isn't available

Features

- Expand your laptop or MacBook connectivity through USB-C by adding three USB-A ports (5Gbps) and a GbE RJ45 port
- Compact, lightweight housing with a small-footprint design for travel or desktop placement
- USB bus-powered and features a built-in USB Type-C cable, so you can carry the hub with you anywhere
- Integrated cable features a small and reversible USB-C connector, and it's Thunderbolt 3 data port compatible
- Multi-platform compatible, with native support in most operating systems including Windows® 10, macOS Sierra (10.12), and Chrome OS™
- Backward compatibility lets you save money by connecting your existing USB 2.0 and 1.x devices
- Offers plug-and-play installation, and supports hot-swapping or hot-plugging
- Supports Wake-On-LAN, Energy-Efficient Ethernet, jumbo frames, full-duplex flow control, VLAN tagging, and layer 2 priority encoding

Hardware	Warranty	2 Years	
	Bus Type	USB 3.0	
	Chipset ID	VIA/VLI - VL812 Realtek - RTL8153	
	Fast-Charge Port(s)	No	
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab IEEE 802.3az Energy-Efficient Ethernet, IEEE 802.3x Flow Control, 802.1q VLAN Tagging, 802.1p Layer 2 Priority Encoding USB 3.0 - Backward compatible with USB 2.0 and 1.1	
	Interface	USB 3.0 RJ45 (Gigabit Ethernet)	
	Ports	3	
	USB-C Device Port(s)	No	
	USB-C Host Connection	Yes	
	Performance	Auto MDIX	Yes
Compatible Networks		10/100/1000 Mbps	
Flow Control		Full duplex flow control	
Full Duplex Support		Yes	
Jumbo Frame Support		9K max.	
Maximum Data Transfer Rate		5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)	
Type and Rate		USB 3.0 - 5 Gbit/s	
UASP Support		Yes	
Connector(s)	Connector Type(s)	3 - USB Type-A (9 pin) USB 3.0 Female 1 - RJ-45 Female 1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Male	
	Software	OS Compatibility	Windows® 7, 8, 8.1, 10 Mac OS X® 10.11 to 10.15 <i>VLAN tagging is currently not supported in Mac OS</i> Linux Kernel 4.11.x <i>LTS Versions only</i>
	Special Notes / Requirements	Note	The hub does not support DisplayPort alt mode, or USB Power Delivery
System and Cable Requirements		Available USB Type-C port - USB 3.0 (5Gbps)	
Power	Power Source	USB-Powered	

Environmental	Humidity	5~90% RH (Non-condensing)
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	5.5 in [140 mm]
	Color	White
	Material	Plastic
	Product Height	0.6 in [1.5 cm]
	Product Length	3.1 in [78 mm]
	Product Width	1.6 in [41 mm]
	Weight of Product	1.3 oz [36 g]
Packaging Information	Package Height	1.3 in [32 mm]
	Package Length	6.8 in [17.2 cm]
	Package Width	5.7 in [14.5 cm]
	Shipping (Package) Weight	3.6 oz [102 g]
What's in the Box	Included in Package	1 - USB 3.0 hub
	Auto-Negotiation	Yes

Product appearance and specifications are subject to change without notice.