

## 7-Port USB-C Hub - Metal - USB-C to 5x USB-A and 2x USB-C - USB 3.0

Product ID: HB30C5A2CST



This USB-C™ hub turns your laptop or desktop USB Type-C™ port into four standard USB-A ports, one USB-A fast-charge port, and two USB-C ports. You can also extend the range of your USB devices by using this hub as a mid-point repeater.

### Connect more devices quickly and easily

The 7-port hub is designed for easy port access when the hub is mounted or sitting on your desk. The hub ports are spaced with enough room between them to easily plug or unplug your USB devices, without having to disconnect other devices from neighboring ports.

With extra USB 3.0 ports, you can increase productivity and connect more devices to your computer, or simply avoid the hassle of swapping connected devices on your port-limited laptop. The hub lets you extend the life of your current USB 3.0 devices while also taking advantage of newer USB-C devices.

It's perfect for IT professionals or anyone who needs to plug and unplug their devices regularly.

## **Enjoy mounted or desktop convenience**

This hub is the perfect accessory for a laptop or desktop workstation, with a rugged metal housing that can withstand the wear and tear of daily use.

With the included wall-mount bracket, you can attach the hub to a surface such as a desktop or a wall, to best suit your needs.

## **Charge-and-sync your mobile devices**

With the available fast-charge port, the hub helps to ensure that your tablet or smartphone are charged and ready to use when you need them. You can also sync and access your device while it's charging. The USB-A charge port supports USB Battery Charging Specification 1.2 and delivers up to 2.4 amps of power, so you can charge your mobile device faster than traditional USB ports allow.

The HB30C5A2CST is backed by a 2-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Installation in locations where USB 3.0 ports need to be securely mounted to a surface, such as on a wall or under a desk
- Upgrade and expand the connection capabilities of your MacBook, Ultrabook™, laptop, or desktop
- Deploy in hot-desk environments to provide USB hub access for multiple devices
- Connect a wide variety of peripherals at home or in the office, all from a single USB 3.0 connection

### Features

- Flexible mounting options, with the included desktop or wall-mount bracket
- Connect two USB-C devices and five USB-A devices to a single USB-C port on your computer
- Supports USB Battery Charging Specification 1.2 and delivers up to 2.4 amps through the USB-A charge port
- USB-A ports are backward compatible with older USB 2.0 and 1.1 devices
- Industrial, metal enclosure
- Integrated physical On/Off power button
- Supports easy plug-and-play installation, hot-swapping or hot-plugging
- All ports are compliant with USB 3.0 and data rates up to 5Gbps

<b>Hardware</b>	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	Realtek - RTS5411
	Fast-Charge Port(s)	Yes
	Industry Standards	USB Battery Charging Specification Rev. 1.2 USB-A charging port delivers up to 2.4 amps of power USB 3.0 - Backward compatible with USB 2.0 and 1.1
	Interface	USB 3.0
	Ports	7
	USB-C Device Port(s)	Yes
	USB-C Host Connection	Yes
<b>Performance</b>	Maximum Data Transfer Rate	5 Gbps
	Type and Rate	USB 3.0 - 5 Gbit/s
<b>Connector(s)</b>	Connector A	1 - USB Type-B (9 pin) USB 3.0 Female
	Connector B	4 - USB Type-A (9 pin) USB 3.0 Female
		2 - USB Type-C (24 pin) USB 3.0 (5Gbps) Female
		1 - USB 3.0 A (Fast-Charge, 9 pin, SuperSpeed) Female
<b>Software</b>	OS Compatibility	OS Independent; No additional drivers or software required
<b>Special Notes / Requirements</b>	<b>Note</b>	The USB Type-C port is data only. USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps. The hub does not support DP Alt Mode or USB Power Delivery.
	System and Cable Requirements	Available USB Type-C port - USB 3.0 (5Gbps)
<b>Indicators</b>	LED Indicators	1 - Power
		7 - Hub Port Connection
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	1.5 A
	Input Voltage	100 ~ 240 AC
	Output Current	3 A
	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	36
	Power Source	AC Adapter Included

<b>Environmental</b>	Humidity	20~80% RH
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	-20°C to 50°C (-4°F to 122°F)
<b>Physical Characteristics</b>	Cable Length	40.2 in [1022.4 mm]
	Color	Black
	Enclosure Type	Aluminum
	Form Factor	Desktop
	Product Height	1 in [26 mm]
	Product Length	5.1 in [130 mm]
	Product Weight	6 oz [170 g]
	Product Width	2.4 in [60 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	22.9 oz [650 g]
<b>What's in the Box</b>	Included in Package	1 - USB-C hub
		1 - universal power adapter (NA/JP, UK, EU, ANZ)
		1 - USB-C to USB-B cable
		2 - rubber feet
		2 - mounting brackets
		4 - mounting screws
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.