

2 Port USB to RS232 Serial DB9 Adapter Cable

Product ID: ICUSB232C2



The StarTech.com ICUSB232C2 2 port USB to DB9 RS232 Serial Adapter Cable lets you connect up to two DB9 RS232 serial devices simultaneously to your Mac or PC laptop or desktop computer through a USB port, as though the computer offered an onboard DB9M connector.

A cost-effective solution that bridges the compatibility gap between modern computers and legacy serial peripherals.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect and program LED and Digital signage boards with serial communication ports

Features

- USB to 2 Port Straight-Through RS232 Serial Adapter
- Easy Plug-and-Play installation
- Bus powered, no external power adapter required
- Fully compliant with USB 1.1 specifications

Hardware	Warranty	2 Years
	Bus Type	USB 2.0
	Chipset ID	Prolific - PL2303HXA Prolific - PL2303RA
	Interface	Serial
	Port Style	Cable Adapters
	Ports	2
Performance	FIFO	192 Bytes
	Maximum Data Transfer Rate	230Kbps
	Serial Protocol	RS-232
Connector(s)	Connector Type(s)	1 - USB Type-A (4 pin) USB 2.0 Male 2 - DB-9 (9 pin, D-Sub) Male
	OS Compatibility	Windows 8-10 is only supported by RevB Windows® CE 4.2, 5.2, 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2016 Mac OS® 10.6 to 10.14 Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
Special Notes / Requirements	System and Cable Requirements	1 USB 1.1 (or above) port
Environmental	Humidity	0~65% RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-20°C to 80°C (-4°F to 176°F)
Physical Characteristics	Cable Length	1 ft [0.3 m]
	Color	Black
	Enclosure Type	Plastic
	Product Length	12.2 in [310 mm]
	Product Weight	4.8 oz [137 g]
Packaging Information	Shipping (Package) Weight	4.8 oz [137 g]
What's in the Box	Included in Package	1 - 2 Port USB to RS232 Serial Cable

Product appearance and specifications are subject to change without notice.