

## 6 ft High Speed HDMI Cable with Ethernet - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMIMM6HS



The HDMIMM6HS 6-foot High Speed HDMI® Cable with Ethernet supports the advanced capabilities of the High-Definition Multimedia Interface, including Ethernet data inter-connectivity with compatible HDMI-enabled products, and is fully backward compatible with older HDMI-capable devices.

The cable features gold-plated HDMI (male) connectors which help to ensure a high quality digital connection capable of transmitting high-definition video and multi-channel audio between devices such as Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, stereo receivers and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

All StarTech.com High Speed HDMI Cables are expertly designed and constructed of top quality materials to deliver dependable high-definition performance, and are backed by Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Quick-connect single HDMI® cable replaces multiple audio and video cables, reducing clutter and hassle
- Connecting high-definition A/V devices such as Blu-Ray Disc™ players, HDTVs, DVRs, etc.
- Connecting HDMI-equipped devices such as DVD players, game consoles, etc.
- Enables multiple devices to share an Internet connection (where applicable, device must support High Speed HDMI® with Ethernet)

### Features

- Gold-plated HDMI® connectors
- High quality construction
- 3D and Ethernet ready (for supported devices)
- Résolutions Ultra HD pouvant atteindre 4k x 2k

|                                   |                             |  |
|-----------------------------------|-----------------------------|--|
|                                   | Warranty                    | Lifetime   |
| <b>Matériel</b>                   | Nombre de conducteurs       | 19   |
|                                   | Placage du connecteur       | Or   |
|                                   | Type de blindage du câble   | Feuille d'aluminium-Mylar avec blindage tressé             |
|                                   | Type de gaine de câble      | PVC - Polyvinyl Chloride                                   |
| <b>Performance</b>                | Résolutions numériques max. | 4K x 2K @ 30 Hz  |
| <b>Connecteur(s)</b>              | Connecteur A                | 1 - HDMI (19 broches) Mâle                                 |
|                                   | Connecteur B                | 1 - HDMI (19 broches) Mâle                                 |
| <b>Caractéristiques physiques</b> | Longueur du produit         | 72 in [1829 mm]  |
|                                   | Calibre du fil              | 28 AWG   |
|                                   | Couleur                     | Noir   |
|                                   | Dia. ext. du câble          | 0.3 in [7.3 mm]  |
|                                   | Longueur de câble           | 6 ft [1.8 m]   |
|                                   | Longueur du produit         | 6 ft [1.8 m]   |
|                                   | Poids du produit            | 4.3 oz [123 g]   |
|                                   | Style de connecteur         | Droit  |
| <b>Informations d'emballage</b>   | Poids brut                  | 4.7 oz [132 g]   |
|                                   | Quantité par paquet         | 1  |
| <b>Contenu du paquet</b>          | Inclus dans le paquet       | 1 - 6 ft High Speed HDMI® Cable with Ethernet - HDMI - M/M |

Product appearance and specifications are subject to change without notice.